

8700 Coax - Miniature

For more Information
please call

1-800-Belden1

**Description:**

Miniature, 28 AWG solid .013" tinned copper conductor, polypropylene insulation, bare copper braid shield (90% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	28	Solid	TC - Tinned Copper	.013

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
PP - Polypropylene	.023

Outer Shield**Outer Shield Material:**

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	90

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 0.054 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Non-UL Temperature Rating: 105°C

Bulk Cable Weight: 3 lbs/1000 ft.

Max. Recommended Pulling Tension: 7 lbs.

Min. Bend Radius (Install)/Minor Axis: 0.600 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMH

CEC/C(UL) Specification: CMH FT1

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
32

Nom. Inductance:

Inductance (µH/ft)
.049

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
55.2

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
66.9

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
28.7

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	2.5
10	7.7
50	17.2
100	24.5
200	34.8
400	50.0
700	66.0
900	75.0
1000	79.0

Max. Operating Voltage - UL:

Voltage
300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8700 010250	250 FT	0.750 LB	BLACK		32 OHM MINIATURE COAX

Revision Number: 2 Revision Date: 12-18-2009

© 2011 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.