



- Document Downloads
- Catalog Page
 - PDF
 - DWF
 - IGS
 - STEP
 - X_B

Super Torq Swage Standoff, Round, Electro Tin - Bright, Brass, 4.7mm Shank OD, M3.0x0.5, 5mm Body Length

Part ID: **BR5114SPC-05.0-43**

Technical Specifications

Material Grade (Alloy):	Brass 360 (ASTM-B-116, QQ-B-626) 353 (ASTM-B-116)	Shank	Length: 3.4mm Outside Diameter: 4.7mm Inside Diameter: 3.74mm Panel Thickness: 2.4mm Code: C
Profile	Round	Panel Hole Size	4.820-4.900
Outside Diameter	6.0mm	Finish Desc. (Spec)	Electro Tin - Bright (ASTM B 545)
Overall Length	8.4mm	Compliant To	RoHS, WEEE, REACH, Conflict Minerals
Female Thread	M3.0x0.5		
Swage Anvil Code	6-2		
Swage Punch Code	188		

Available Finishes	
43 - Electro Tin - Bright	▼

Product Description

Super-Torq Swage parts are designed to resist rotation under high assembly torques and to eliminate breaks in electrical connections due to spinning of standoffs during assembly. The unique Super-Torq corner knurl prevents the fastener from twisting after installation. Lyn-Tron standard swaging tools can be used on Super-Torq standoffs in the same way as installing conventional swage standoffs for an easy upgrade. The round shape provide a nice finished look. Brass is corrosion resistant, nonmagnetic, and easily machinable. Base metal is yellow, but many plating options are available when different colors are required.

Stock and Lead Time

Stock	0	Available
Stock to Plate	0	2 to 3 weeks
Manufacture Lead Time	12-13	Weeks