

FL SWITCH LM 4TX/2FX-E

Order No.: 2891660



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2891660>

Ethernet lean managed switches with four RJ45 ports, 10/100 Mbps, with auto crossing and auto negotiation and two glass fiber SC FO ports (multimode), 100 Mbps (100BASE-FX), SNMP management, redundancy via Rapid Spanning Tree (IEEE 802.1w) and Fast Ring Detection, multicast filtering, VLAN, IGMP snooping, 24 V DC power supply, redundant

Commercial data

GTIN (EAN)	
sales group	K000
Pack	1 pcs.
Customs tariff	85176200
Catalog page information	Page 182 (AX-2009)

Product notes

WEEE/RoHS-compliant since:
03/27/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Product description

The compact lean managed switches (LM) make it possible to set up flexible and economical managed Ethernet networks in an automation environment. Its huge range of connection variants and extended temperature range of -40 °C to +70 °C enable it to perfectly cover the requirements of industrial applications. The integrated software allows networks to be redundantly set up, diagnosed and monitored using IT standard protocols.

Technical data

Interfaces

Interface	Ethernet (RJ45)
No. of ports	4 (RJ45 ports)
Type of connection	RJ45 female connector, auto negotiation
Transmission physics	Copper
Transmission speed	10/100 MBit/s (RJ45)
Interface	Fiber optic interface
No. of ports	2 (SC multimode)
Type of connection	SC duplex
Transmission length	11000 m (glass fiber with F-G 62.5/125 0.7 dB/km F1000)
	6400 m (glass fiber with F-G 50/125 0.7 dB/km F1200)
	3000 m (glass fiber with F-G 62.5/125 2.6 dB/km F600)
	2800 m (glass fiber with F-G 50/125 1.6 dB/km F800)
Interface	Serial (V.24 (RS-232))
Type of connection	V.24 (RS-232-C), 6-pos. MINI-DIN female connector (PS/2)

Function

Basic functions	Store-and-forward switch, IGMP v2, GMRP
Supported browsers	Internet Explorer 5.5 or higher
Redundancy	Rapid Spanning Tree 802.1w, Fast Ring Detection
Status and diagnostic indicators	Per Ethernet 2 status LEDs: LINK and status activity, 100, full duplex, supply voltage U_{S1} and U_{S2} (redundant supply voltage)

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length ((twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	18.5 V DC ... 30.5 V DC
Typical current consumption	400 mA (at $U_s = 24$ V DC)

General data

Weight	230 g
Width	45 mm

Height	99 mm
Depth	112 mm
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	30 % ... 95 % (no condensation)
Permissible humidity (storage/transport)	30 % ... 95 % (no condensation)
Air pressure (operation)	80 kPa ... 108 kPa (2000 above sea level)
Air pressure (storage/transport)	70 kPa ... 108 kPa (3000 above sea level)
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005

Certificates / Approvals



Certification	CUL, UL
Certification Ex:	CUL-EX LIS, UL-EX LIS

Accessories

Item	Designation	Description
Cable/conductor		
2832250	FL CAT5 PATCH 0,3	Patch cable, CAT5, assembled, 0.3 m
2832263	FL CAT5 PATCH 0,5	Patch cable, CAT5, assembled, 0.5 m
2832276	FL CAT5 PATCH 1,0	Patch cable, CAT5, assembled, 1.0 m
2832221	FL CAT5 PATCH 1,5	Patch cable, CAT5, assembled, 1.5 m
2832629	FL CAT5 PATCH 10,0	Patch cable, CAT5, assembled, 10.0 m
2832289	FL CAT5 PATCH 2,0	Patch cable, CAT5, assembled, 2.0 m
2832292	FL CAT5 PATCH 3,0	Patch cable, CAT5, assembled, 3.0 m
2832580	FL CAT5 PATCH 5,0	Patch cable, CAT5, assembled, 5.0 m
2832616	FL CAT5 PATCH 7,5	Patch cable, CAT5, assembled, 7.5 m

Female insert

1654358	VS-SCRJ-GOF-KU	SCRJ coupling insert, duplex, for VS-PP-19-1HE-16-F patch panel and VS-TO...F...terminal outlets and VS-SI-FP-2F front plate, can be used for glass multi-mode, HCS and polymer fiber types
---------	----------------	---

General

0800886	E/NS 35 N	End clamp, width: 9.5 mm, color: gray
2891165	FL PF 2TX CAT5E	Patch field with two RJ45 CAT5e network connections
2891178	FL PF 8TX CAT5E	Patch field with eight RJ45 CAT5e network connections
2832991	FL RJ45 PROTECT CAP	Dust protection caps for RJ45 female connector
2832865	FL SEC PAC 4TX	Layer1 security elements for four RJ45 network connections for use with patch boxes and panels
1654400	VS-PC-2XGOF-50-SCRJ/SCDU-1	Assembled fiber optic cable, break-out cable, glass fiber multi-mode 50/125 µm, SCRJ/IP20 on SC-duplex/IP20, for installation inside control cabinets, length: 1 m

Plug/Adapter

2744571	FL PLUG RJ45 GN/2	RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.
2744856	FL PLUG RJ45 GR/2	RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.
2730611	PRG CAB MINI DIN	Connection cable, to connect Remote Field Controllers to a PC (RS-232) for PC WORX, 3 m in length

Software

2832166	FL SNMP OPC SERVER	SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems
2831044	FL SWT	Factory Manager, multilingual, configuration and diagnostics software for ETHERNET networks in automation

Tools

2744869	FL CRIMPTOOL	Crimping pliers, for assembling the RJ45 connectors FL PLUG RJ45..., for assembly on site
---------	--------------	---

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;