


NSD10 (Time-delay)

RoHS *1


AC32V



Scale: 1/1



Unit: mm



The I-t curves above are plots of the average values of measurements obtained under conditions specified by SOC. These data are for reference only and are not intended to infer any guaranteed values.

| Rated voltage | Certification | Range of rated current (I_N) *2 | Rated breaking current | | Current carrying capacity | Temp. rise | Overload operation |
|---------------|--------------------------------|-------------------------------------|------------------------|-----------------|---------------------------------------------------------------------|--------------------------|-----------------------------------------------------------------|
| AC32V | UL Recognized CSA Certified | Over 8A - 15A | 3000A | PF 0.7 - 0.8 | 1.1 I_N for 15min or more after temperature stabilization occurs. | 70K or less at 1.1 I_N | Within 60min at 1.35 I_N 12s - 2min inclusive at 2.0 I_N |

*1: High melting temperature type solder containing more than 85 wt% lead is used in this product.

*2: Any rated current value can be selected within this range.

DCSU2 (Normal-acting)

Over 5A - 15A:

RoHS

Pb

Over 15A - 20A:


RoHS

*1


DC60V



Scale: 1/1



Unit: mm



The I-t curves above are plots of the average values of measurements obtained under conditions specified by SOC. These data are for reference only and are not intended to infer any guaranteed values.

| Rated voltage | Certification | Range of rated current (I_N) *2 | Rated breaking current | | Current carrying capacity | Temp. rise | Overload operation |
|---------------|---------------|-------------------------------------|------------------------|-------------------|---------------------------------------------------------------------|------------|--------------------------------------------------------|
| DC60V | UL Recognized | Over 5A - 20A | 100A | Resistive circuit | 1.0 I_N for 15min or more after temperature stabilization occurs. | — | Within 60min at 1.35 I_N Within 2min at 2.0 I_N |

*1: High melting temperature type solder containing more than 85 wt% lead is used in this product (over 15 A - 20 A).

*2: Any rated current value can be selected within this range.