



HMHR-A

.050" X .050"

STRAIGHT PCB MOUNT




A = .050 [1.27] X No. of Spaces + .233 [5.92]

B = .050 [1.27] X No. of Spaces

C = .050 [1.27] X No. of Spaces + .621 [15.77]



HMHR-A-50-VUAS





Recommended PCB Layout

HMHR-A

.050" X .050"


RIGHT ANGLE PCB MOUNT




A = .050 [1.27] X No. of Spaces + .233 [5.92]

B = .050 [1.27] X No. of Spaces

C = .050 [1.27] X No. of Spaces + .621 [15.77]



HMHR-A-34-HUAS





Recommended PCB Layout

HMHR-A

.050" X .050"


VERTICAL SMT




A = .050 [1.27] X No. of Spaces + .233 [5.92]

B = .050 [1.27] X No. of Spaces

C = .050 [1.27] X No. of Spaces + .621 [15.77]



HMHR-A-60-VUAS-SMT



Recommended PCB Layout