





Frame	Aluminum Die-cast	Notes
Impeller	Metal alloy	Date: 050113
Connection *	Lead wires or Terminal	Environmental Protection: IP55 Storage Temp: -40C ~ +100C Weight: 630g (1.39 lbs)
Motor	AC Shaded pole, Impedance protected	
Bearing System	Dual Ball bearing	
Insulation Resistance	>100MOhm at 500VDC	Available AC voltages by special order: 12, 24, 28, 38, 42, 48, 440, 480. Dual speed also available. Call for information.
Dielectric Strength	> 60 seconds at 1500VAC	
Operating Temp Range	-30C ~ +80C (non-condensing)	* Specify configuration: TB = Terminal, Ball bearing WB = Wire leads, Ball bearing
Life Expectancy	50000 hours (55C)	



Model No.	Func. Code	Speed (RPM)	Airflow (CFM)	Noise	Volts AC	Voltage Range AC	Watts	Max. Static Pressure ("H ₂ O)	Curves
OA119AP-11-1 *	1855	2600 2950	110 128	48	115	100 ~ 120	29 26	0.27 0.29	2 (50Hz) 1 (60Hz)
OA119AP-11-2 *	1855	2300 2400	95 105	42	115	100 ~ 120	23 20	0.23 0.25	4 (50Hz) 3 (60Hz)
OA119AP-11-3 *	1855	1600 1500	68 65	28	115	100 ~ 120	18 15	0.18 0.16	6 (50Hz) 5 (60Hz)
OA119AP-22-1 *	1855	2600 2950	110 128	48	230	200 ~ 240	29 26	0.27 0.29	2 (50Hz) 1 (60Hz)
OA119AP-22-2 *	1855	2300 2400	95 105	42	230	200 ~ 240	23 20	0.23 0.25	4 (50Hz) 3 (60Hz)
OA119AP-22-3 *	1855	1600 1500	68 65	28	230	200 ~ 240	18 15	0.18 0.16	6 (50Hz) 5 (60Hz)