

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

- INSULATOR MATERIAL: THERMOPLASTIC UL94V0
- CONTACT MATERIAL: BRASS (SIGNAL CONTACT)
- BRASS (POWERS CONTACT)
- ACCESSORIES: BRASS
- SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

- NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)
- 30A or 40A (POWER CONTACT)
- CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL and POWER)
- CONTACT/CONTACT : >=1000 V
- CONTACT/GROUND : >=1200 V
- INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21
- TEMPERATURE RANGE -55°C TO +125°C
- DAMP HEAT STEADY STATE 21 DAYS
- SALT SPRAY 24 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m maximum
- Female screw : 0.5 N.m maximum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-47-0004.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec:
 - Signal contacts: Ni + Gold/GxT
 - Power contacts: Ni 1.27µmi+Sn 2.5 to 7.5µ,pure bright
- Active area plating spec:
 - Signal and power contacts: Ni + Gold/GxT
- Shell plating :2 to 4µm Cu + Ni + 3 to 10µmm Sn,pure bright
- Accessories: Sn pure bright + nickel
- Packaging spec: See GS-14-920

Series

Shell size: **E A B C**
(see sheet 3)

Front accessory definition
(see sheet 2)

- blank**:without accessory
- L** :threaded insert M3
- O** :threaded insert UNC 4-40
- V** :female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts
P Pin

Termination type
5 Right angle/Europe standard

Plating
00 200 matings/unmatings
43 500 matings/unmatings

PCB accessories definition(see sheet 2)
A :without accessory
H :Metal brackets+harpoons for PCB 2.40mm
G :Metal brackets+harpoons for PCB 1.60mm
M :Metal brackets


Power contacts
30 :Fitted with power contacts 30 Amp.
40 :Fitted with power contacts 40 Amp.

DBL13W3P500G30LF

See note RoHS

TABLE 1:PCB HOLE DIAMETERS


POWER CONTACTS			ACCESSORIES	SIGNAL CONTACT
30 A	2.00	Ø2.40	Ø3.10	Ø1.00
40 A	2.80	Ø3.10		
Max current Power	ØA±0.10	PCB HOLE ±0.10	PCB HOLE ±0.10	PCB HOLE ±0.10




spec ref		dr		1, Product Eng	2015/06/16	projection 	mm 	size	A2	scale	1:1		
tolerance std		eng		Gregar Mathew	2019/11/11			ecn no	ELX-1-33009-1				
ISO 1101 ISO 406		chr		-	-				Released				
		appr		Varma Sudhir	2019/11/12	product family		-					
surface		linear	0.X		±0.3	Amphenol FCI	SUB MALE DW EUROPE FOOT PRINT		dwg no	C01-8639-2304c		rev	E
			0.XX		±0.10.10								
			0.XXX		±0.05								
ISO 1302		angular	0°		±2°	cat. no.		-	Product - Customer Drw		sheet 1 of 7		

Amphenol
FCi

© 2016 AFCI



FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
PCB ACCESSORIES	A Without	A Without	A Without	M Metal brackets	M Metal brackets	M Metal bracket



FRONT ACCESSORY	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40	Blank Without	L insert M3 O insert UNC 4.40	V insert UNC 4.40
PCB ACCESSORIES	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm

spec ref			dr		1, Product Eng	2015/06/16	projection		mm		size	A2	scale	3:1		
tolerance std			eng		Gregar Mathew		2019/11/11				ecn no		ELX-133009-1			
ISO 1101			chr		-		-				rel level		Released			
ISO 1101			appr		Varma Sudhir		2019/11/12		product family		-					
ISO 406																
surface			linear		Amphenol FCI		title		SUB MALE DW EUROPE FOOT PRINT		dwg no		C01-8639-2304c		rev	
			0.X													
0.XX		±0.10														
0.XXX		±0.05														
ISO 1302			angular		0°		±2		cat. no.		-		Product - Customer Drw		sheet 2 of 7	

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP500A30LF	30	200	without	without
D*LxWxP500A30LF	30	200	insert M3	without
D*OxWxP500A30LF	30	200	insert UNC 4.40	without
D*VxWxP500A30LF	30	200	female screw UNC 4.40	without
D*xWxP500H30LF	30	200	without	metal bracket+harpoon PCB 2.40mm
D*LxWxP500H30LF	30	200	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxP500H30LF	30	200	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxP500H30LF	30	200	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxP500G30LF	30	200	without	metal bracket+harpoon PCB 1.60mm
D*LxWxP500G30LF	30	200	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxP500G30LF	30	200	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxP500G30LF	30	200	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxP500M30LF	30	200	without	metal bracket
D*LxWxP500M30LF	30	200	insert M3	metal bracket
D*OxWxP500M30LF	30	200	insert UNC 4.40	metal bracket
D*VxWxP500M30LF	30	200	female screw UNC 4.40	metal bracket


PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP500A40LF	40	200	without	without
D*LxWxP500A40LF	40	200	insert M3	without
D*OxWxP500A40LF	40	200	insert UNC 4.40	without
D*VxWxP500A40LF	40	200	female screw UNC 4.40	without
D*xWxP500H40LF	40	200	without	metal bracket+harpoon PCB 2.40mm
D*LxWxP500H40LF	40	200	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxP500H40LF	40	200	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxP500H40LF	40	200	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxP500G40LF	40	200	without	metal bracket+harpoon PCB 1.60mm
D*LxWxP500G40LF	40	200	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxP500G40LF	40	200	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxP500G40LF	40	200	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxP500M40LF	40	200	without	metal bracket
D*LxWxP500M40LF	40	200	insert M3	metal bracket
D*OxWxP500M40LF	40	200	insert UNC 4.40	metal bracket
D*VxWxP500M40LF	40	200	female screw UNC 4.40	metal bracket

shell size
*
E
A
A
B
B
B
C
C
C

LAYOUTS
xWx
5W1
11W1
7W2
21W1
17W2
13W3
9W4
25W3
21WA4
27W2

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP543A30LF	30	500	without	without
D*LxWxP543A30LF	30	500	insert M3	without
D*OxWxP543A30LF	30	500	insert UNC 4.40	without
D*VxWxP543A30LF	30	500	female screw UNC 4.40	without
D*xWxP543H30LF	30	500	without	metal bracket+harpoon PCB 2.40mm
D*LxWxP543H30LF	30	500	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxP543H30LF	30	500	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxP543H30LF	30	500	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxP543G30LF	30	500	without	metal bracket+harpoon PCB 1.60mm
D*LxWxP543G30LF	30	500	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxP543G30LF	30	500	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxP543G30LF	30	500	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxP543M30LF	30	500	without	metal bracket
D*LxWxP543M30LF	30	500	insert M3	metal bracket
D*OxWxP543M30LF	30	500	insert UNC 4.40	metal bracket
D*VxWxP543M30LF	30	500	female screw UNC 4.40	metal bracket




PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxP543A40LF	40	500	without	without
D*LxWxP543A40LF	40	500	insert M3	without
D*OxWxP543A40LF	40	500	insert UNC 4.40	without
D*VxWxP543A40LF	40	500	female screw UNC 4.40	without
D*xWxP543H40LF	40	500	without	metal bracket+harpoon PCB 2.40mm
D*LxWxP543H40LF	40	500	insert M3	metal bracket+harpoon PCB 2.40mm
D*OxWxP543H40LF	40	500	insert UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*VxWxP543H40LF	40	500	female screw UNC 4.40	metal bracket+harpoon PCB 2.40mm
D*xWxP543G40LF	40	500	without	metal bracket+harpoon PCB 1.60mm
D*LxWxP543G40LF	40	500	insert M3	metal bracket+harpoon PCB 1.60mm
D*OxWxP543G40LF	40	500	insert UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*VxWxP543G40LF	40	500	female screw UNC 4.40	metal bracket+harpoon PCB 1.60mm
D*xWxP543M40LF	40	500	without	metal bracket
D*LxWxP543M40LF	40	500	insert M3	metal bracket
D*OxWxP543M40LF	40	500	insert UNC 4.40	metal bracket
D*VxWxP543M40LF	40	500	female screw UNC 4.40	metal bracket

spec ref		dr		1, Product Eng	2015/06/16			size	A2	scale	3:1
tolerance std		eng		Gregar Mathew	2019/11/11			ecn no	ELX-133009-1	rel level	Released
ISO 1101		chr		-	-						
ISO 406		appr		Varma Sudhir	2019/11/12						
TOLERANCES UNLESS OTHERWISE SPECIFIED		Amphenol FCI		SUB MALE DW EUROPE FOOT PRINT				C01-8639-2304c		rev	
surface		linear		0.X ±0.30		MIXED POWER RIGHT ANGL SOLDER		01-8639-2304c		E	
ISO 1302		angular		0° ±0.05		cat. no.		-		Product - Customer Drw	
										sheet 3 of 7	

5W1

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I






Floating signal contacts

11W1

LAYOUT AND CONNECTOR DIMENSIONS




For PCB hole diameters see table I sheet I





7W2

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I







SIDE VIEW FOR ALL LAYOUTS



spec ref		dr		1, Product Eng		2015/06/16		projection		mm		size		scale							
tolerance std		eng		Gregar Mathew		2019/11/11						A2		2:1							
ISO 1101		chr		-		-						ecn no		ELX-133009-1							
ISO 406		appr		Varma Sudhir		2019/11/12						product family		D SUB -		rel level		Released			
surface		linear		0.X		±0.30		Amphenol FCi		title		SUB MALE DW EUROPE FOOT PRINT		dwg no		C01-8639-2304c		rev			
ISO 1302				0.XX		±0.10														MIXED POWER RIGHT ANGL SOLDER	
				0.XXX		±0.05															
		angular		0°		±0.2															





13W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



9W4





LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



Floating signal contacts

17W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



spec ref				dr		1, Product Eng		2015/06/16		projection		mm		size		A2		scale		2:1							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Gregar Mathew		2019/11/11						ecn no		ELX-1-33009-1		rel level		Released							
ISO 1101				chr		-		-																			
ISO 406				appr		Varma Sudhir		2019/11/12																			
										product family		D SUB -															
surface		linear		Amphenol FCI		title		SUB MALE DW EUROPE FOOT PRINT		cat. no.		-		Product - Customer Drw		C01-8639-2304c		sheet 5 of 7		rev		E					
																								0.X		±0.30	
																								0.XX		±0.10	
																				</							

21W1



LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I

27W2

LAYOUT AND CONNECTOR DIMENSIONS


For PCB hole diameters see table I sheet I



spec ref			dr		1. Product Eng		2015/06/16		projection		mm		size		A2		scale		2:1							
tolerance std			eng		Gregar Mathew		2019/11/11						ecn no		ELX-133009-1		rel level		Released							
ISO 1101			chr		-		-																			
ISO 406			appr		Varma Sudhir		2019/11/12														product family		D SUB-			
surface			linear		0.X		±0.30		Amphenol FCI		title		SUB MALE DW EUROPE FOOT PRINT		dwg no		C01-8639-2304c		rev		E					
																							0.XX		±0.10	
																							0.XXX		±0.005	
																							angular		0°	
ISO 1302									cat. no.		-		Product - Customer Drw		sheet 6 of 7											


21WA4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



25W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



spec ref		dr		1, Product Eng		2015/06/16		projection		size		scale					
tolerance std		eng		Gregar Mathew		2019/11/11				A2		2:1					
ISO 1101 ISO 406		chr		-		-				ech no		ELX-133009-1					
		appr		Varma Sudhir		2019/11/12		product family		-		rel level					
												Released					
surface		linear		Amphenol FCi		title		SUB MALE DW EUROPE FOOT PRINT MIXED POWER RIGHT ANGL SOLDER		dwg no		C01-8639-2304c		rev			
		0.X														±0.30	
		0.XX														±0.10	
		0.XXX		±0.05													
ISO 1302		angular		0°		±2°		cat. no.		-		Product - Customer Drw		sheet 7 of 7			