






Major League Electronics .079 cl Terminal Strip Headers - Right Angle



Tails may be clipped to achieve desired pin length

Ordering Information



Pins Per Row
01 - 40
Row Specification
S = Single Row

Pin Options				
Tail With .126 Post		Tail With .146 Post		
.120	3.05mm	.100	2.54mm	01
.140	3.56mm	.120	3.05mm	02
.160	4.06mm	.140	3.56mm	04
.199	5.05mm	.179	4.55mm	05
.298	7.57mm	.278	7.06mm	06
.318	8.08mm	.298	7.57mm	08
.337	8.56mm	.317	8.05mm	10

Post Height
A = .126 (3.20)
B = .146 (3.71)

Every Other Pin Filled
Leave blank if not needed
E = Filled

Polarized Position
Leave blank if not needed
If required, specify empty pin position, e.g. 012 for Pin 12


Lock Tight "LT" Option
Leave blank if not needed
LT = With

Plating Options	
G	10µ Gold on Contact Area / Flash on Tail
T	Matte Tin All Over
GT	10µ Gold on Contact Area / Matte Tin on Tail
H	30µ Gold on Contact Area / Matte Tin on Tail
F	Gold Flash over Entire Pin

Specifications
 Current Rating: 3.0 Ampere
 Insulation Resistance: 1000MΩ Min.
 Dielectric Withstanding: 500V AC
 Contact Resistance: 20 mΩ Max.
 Operating Temperature: -40°C to + 105°C
 Max. Process Temperature:
 Peak: 260°C up to 10 secs.
 Process: 230°C up to 60 secs.
 Wave: 260°C up to 6 secs.
 Manual Solder: 350°C up to 5 secs.

Materials
 Contact Material: Phosphor Bronze
 Insulator Material: Nylon 6T
 Plating: Au or Sn over 50µ" (1.27) Ni

Mates with
 BCSS,
 BSSH,
 BSSHC,
 BSSQ,
 BSSQC,
 BSSQM,
 LSMBC,
 LSSHSM,
 SMBC,
 SSHQ,
 SSHQR,
 SSHR,
 SSHS,
 SSHSM,
 ULSMBC



Products cut to specific sizes are uncancellable/nonreturnable Parts are subject to change without notice

TSHR-2-S SERIES .079cl Single Row - Right Angle Terminal Strip Headers 21 FEB 07 Scale NTS

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS IN INCHES (MM)
 TOLERANCES ARE:
 ONE PLACE DECIMALS ±.100
 TWO PLACE DECIMALS ±.010
 THREE PLACE DECIMALS ±.005
 FOUR PLACE DECIMALS ±.0020
 ANGLES ±3°



4235 Earnings Way, New Albany, Indiana, 47150, USA
 1-800-782-3486 (USA/Canada/Mexico)
 Tel: 812-944-7244
 Fax: 812-944-7268
 E-mail: mle@mlelectronics.com
 Web: www.mlelectronics.com

Edition 1
 Sheet 1/1