




1. THIS RECEPTACLE WILL MATE WITH ANY 21C4, SIZE 4 PLUG IN AMPLIMITE SERIES.
2. MAXIMUM WIRE INSULATION TO BE USED WITH THIS RECEPTACLE IS .068 DOA.
3. STAINLESS STEEL RETENTION CLIPS (17) ARE INCLUDED IN INSERT ASSEMBLY.
4. THIS CONNECTOR ACCEPTS SIZE 20 SOCKET SIGNAL CONTACTS.
5. USE 4 SIZE AND POWER OR COAX SOCKET CONTACTS. CONSULT PRODUCT ENGINEERING FOR MORE DETAILS.

- 6 FINISH: CADMIUM PER QQ-P-416.
- 7 FINISH: ZINC PLATED PER ASTM-B-633 .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+).



7	5-445726-1
6	445726-1
REMARKS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHUEY 1-21-88	Tyco Electronics Corporation Harriaburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK A. EMADI 11-10-88	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	PRODUCT SPEC	
0 PLC ± -		APVD	APPLICATION SPEC	
1 PLC ± -		APVD	RESTRICTED TO	
2 PLC ± -		APVD	SIZE	
3 PLC ± .005		APVD	CAGE CODE	
4 PLC ± -		APVD	DRAWING NO	
ANGLES ± -		APVD	REV	
FINISH		APVD	SCALE	
MATERIAL		APVD	SHEET	
SEE CALLOUTS		APVD	OF	
SEE CALLOUTS		APVD	1	
CUSTOMER DRAWING		APVD	REV	
CUSTOMER DRAWING		APVD	B	