


□ MN101C86G

Type	MN101C86G (under development)
ROM (x8-bit)	128 K
RAM (x8-bit)	6 K
Package	QFP100-P-1818B *Lead-free
Minimum Instruction Execution Time	0.1 μ s (at 2.7 V to 3.6 V, 10 MHz) 62.5 μ s (at 2.2 V to 3.6 V, 32 kHz) *
Interrupts	• RESET • Watchdog • External 0 • External 1 • External 2 • External 3 • External 4 • External 5 • External 6 (key interrupt common use) • Timer 0 • Timer 1-1 • Timer 1-2 • Timer 3-2 • Timer 4 • Timer 5 • Serial 0 • Serial 1 • Serial 2 • Serial 3 • Serial 4 • Serial 5 • DMA Transfer Completion (3Lines) • PWM 1 • VBI 1 • VBI 2 • XDS 1 • XDS 2 • Vsync
Timer Counter	Timer counter 0 : 16-bit \times 1 Function Timer function, Clock function Timer counter 1 : 16-bit \times 1 or 8-bit \times 2 Function Timer function Timer counter 2 : 22-bit \times 1 Function Watchdog function, Oscillation stabilization wait function Timer counter 3 : 16-bit \times 1 or 8-bit \times 2 Function Timer function, Remote control transmission function Timer counter 4 : 16-bit \times 1 Function Timer function, Remote control reception function Timer counter 5 : 16-bit \times 1 Function Timer function, Timer pulse output
Serial Interface	Serial interface 0 : 8-bit \times 1 Function Synchronous / Asynchronous switchable Serial interface 1 : 8-bit \times 1 Function Synchronous / Asynchronous switchable Serial interface 2 : 8-bit \times 1 Function Synchronous / Asynchronous switchable Serial interface 3 : 8-bit \times 1 Function Synchronous / Asynchronous switchable, Remote control transmission interface Serial interface 4 : 8-bit \times 1 Function Synchronous / Asynchronous switchable, Remote control reception interface Serial interface 5 : 8-bit \times 1 Function I ² C (master transmission / master reception), Standard mode / Fast mode
Synchronization Signal Separation Function	
Synchronization Judgement Function	

VBI Data Slicer Function	Europe	TELETEXT, VPS, PDC, WSS
	North America	CC, XDS, XDS (x 2)
	Japan	EPG-J, VBID
I/O Pins	I/O	87 • Common use • Input/output selectable (each individual pin)
A/D Inputs		8-bit x 8-ch. (sample / hold function)
PWM		8-bit x 2 (interrupt function, no additional bit)
Special Ports		Output of remote control career, Large current capacity port (LED x 10)
Pin Assignment		



QFP100-P-1818B *Lead-free

Support Tool

In-circuit Emulator	PX-ICE101E + PX-PRB101C86-QFP100-P-1818B-M	
Flash Memory Built-in Type	Type	MN101CF86G (under development)
	ROM (x 8-bit)	128 K
	RAM (x 8-bit)	6 K
	Minimum instruction execution time	0.1 μ s (at 2.7 V to 3.6 V, 10 MHz) 62.5 μ s (at 2.2 V to 3.6 V, 32 kHz)
	Package	QFP100-P-1818F *Lead-free

Request for your special attention and precautions in using the technical information and semiconductors described in this material

(1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technical information described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.

(2) The technical information described in this material is limited to showing representative characteristics and applied circuits examples of the products. It neither warrants non-infringement of intellectual property right or any other rights owned by our company or a third party, nor grants any license.

(3) We are not liable for the infringement of rights owned by a third party arising out of the use of the technical information as described in this material.

(4) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).

Consult our sales staff in advance for information on the following applications:

- Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
- Any applications other than the standard applications intended.

(5) The products and product specifications described in this material are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.

(6) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage, and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.

Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.

(7) When using products for which damp-proof packing is required, observe the conditions (including shelf life and amount of time let standing of unsealed items) agreed upon when specification sheets are individually exchanged.

(8) This material may be not reprinted or reproduced whether wholly or partially, without the prior written permission of Matsushita Electric Industrial Co., Ltd.