


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECO-15-015185	16NOV2016	SY	SY

D

C

B

A




- 1 GOLD PLATE PER MIL-0-45204 .000001 MIN. THK. OVER NICKEL PLATE.
- 2 GOLD PLATE PER MIL-G-45204 .000015 MIN. THK. OVER NICKEL PLATE.
- 3 PLATING IS NOT RREQUIRED ON CARRIER STRIP.
4. POST DIAGONAL .0310/.0350 AFTER PLATING
5. QUANTITY PER REEL-25,000
- 6 ACTION PIN AREA.
- 7 GOLD PL. PER MIL-G-45204 .000030 MIN. THK. OVER NICKEL PL.
- 8 GOLD PL. PER QQ-N-290 .000050 MIN. THK.
- 9 SOLDER PL. .000100 MIN. THK. OVER NICKEL PL.
- 10 MATTE TIN PL. .000100 MIN. THK. OVER NICKEL PL.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



D

C

B

A



AMP 6-14018 14019, CABLE CIFIC E ADATIONS	11	OBSOLETE	—	.160		.965	.475	7-117285-3		
			119328	—			.965	.475	6-117285-8	
			—	.160	UNPLATED		.965	.475	2-117285-7	
			—							
			—	.405			1.192	.702	2- OBSOLETE -5	
			—	.190			.965	.475	2	4
			—	.160			.965	.475	2	3
			—	.415			1.192	.702	2- OBSOLETE -2	
			—	.200			.965	.475	2- OBSOLETE -1	
			119529	.160			.965	.475	2	0
			119330	—			1.192	.702	1	9
			119328	—			.965	.475	1-117285-8	
			COMB NO.	DETAIL C(D)	FINISH	B	A	PART NO.		

OBSOLETE

	-		1.192	.702	1- OBSOLETE -7
	-		.965	.475	1- -6
	-		.965	.475	1- OBSOLETE -5
			1.192	.702	1- OBSOLETE -4
	.190		.965	.475	1- -3
	.160		.965	.475	1- -2
	.415		.965	.475	1- OBSOLETE -1
	.200		.965	.475	1- OBSOLETE -0
	.160		.965	.475	-9
	-		1.192	.702	117285-8
	-		.965	.475	117285-7
	-		1.192	.702	117285-5
	-		.965	.475	117285-2
COMB NO.	DETAIL C(D)	FINISH	B	A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
COPPER-NICKEL-TIN ALLOY STRIP
COPPER ALLOY NO.725
SPRING TEMPER

FINISH

DWN
-
CHK
-
APVD
-

PRODUCT SPEC
-
APPLICATION SPEC
-

WEIGHT
0

CUSTOMER DRAWING

TE Connectivity

NAME
CONTACT, ECONOMATE I
(.156 X .200 CL.)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-117285

RESTRICTED TO
-

SCALE
6:1

SHEET
1 OF 1

REV
L