





30

5



SECTION A-A



SECTION B-B
TYP SERRATION

TERMINAL ACCEPTS ONE(1) #18 MAGNET WIRE
& ONE(1) #20 1/2 MAGNET WIRE
REF AMP PART # 505018-1

Unpublished copy not to be reproduced nor published
without written permission of AMP Incorporated

LOC 50
AF 50
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

REVISION RECORD				REQUIRED PER ASSEMBLY				DWG SIZE		NUMBER		NAME		REMARKS		ITEM NO	
D	REVISE PER ECR-13-013738	GRZ	JL	15FEB2014													
C	REV PER 0710-0427-95	PMF		24/6/95													
B	RESTORATION	ST	KB	5/23/85													
B	ADD SECT B-B, M-6405	MS	DH	7/28/81													
A	PMVD RESTORATION 14-5548	LVS	EW	9/11/71													
LTR	REVISION RECORD	DR	CHK	DATE													
								DWG SIZE		NUMBER		NAME		REMARKS		ITEM NO	
								© 1972 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.						CUSTOMER COPY REFERENCE ONLY			
								DR <i>HILLBISH</i> 11/15/72				MATERIAL AND FINISH .020 THICK BRASS		AMP INCORPORATED HARRISBURG, PENNA.			
								CHK						CLASS			
								DE <i>H.B. Hillbush</i> 11/16/72				WIRE - RANGE - INSULATION 20-16 MAGNET		TYPE			
								APP <i>B.T. Pollock</i> 1/3/73				TOLERANCE EXCEPT AS NOTED ±.015 ±1° 0'		SCALE 4x1		LOC CM B	
												NAME STUD RETAINING TERMINAL AMPLIVAR		NO 505044		REV D	