





PRODUCT NUMBER	NUMBER OF POS.	DIW"C"	DIW"D"
71998-Y02(H)LF	2 x 02	2.54	5.00
71998-Y03(H)LF	2 x 03	5.08	7.54
71998-Y04(H)LF	2 x 04	7.62	10.08
71998-Y05(H)LF	2 x 05	10.16	12.62
71998-Y06(H)LF	2 x 06	12.70	15.16
71998-Y07(H)LF	2 x 07	15.24	17.70
71998-Y08(H)LF	2 x 08	17.78	20.24
71998-Y09(H)LF	2 x 09	20.32	22.78
71998-Y10(H)LF	2 x 10	22.86	25.32
71998-Y13(H)LF	2 x 13	30.48	32.94

- ROHS COMPATIBLE, SEE NOTE 4
WHEN NEEDED, SUFFIX LETTER "H"
INDICATES IT'S A HIGH TEMPERATURE PRODUCT
SEE NOTE 2

NOTES:

- 1 - MATERIAL, HOUSING: THERMOPLASTIC POLYESTER 30% GLASS FILLED COLOUR BLUE. FLAME RETARDANT PER UL-94 CATEGORY VO
- 2 - MATERIAL, HOUSING: HIGH TEMPERATURE THERMOPLASTIC 30% GLASS FILLED, COLOUR GREY. FLAME RETARDANT PER UL-94 CATEGORY VO.
- 3 - MATERIAL TERMINAL: PHOSPHOR BRONZE EXTRA HARD.
- 4 - ROHS COMPATIBLE PRODUCT SPECIFICATIONS
- a - PLATING:
 - "L⁺" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTER TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - END STAND-OFFS FOR 2x2 UP TO 2x5 POS
NO END STAND-OFFS FOR 2x6 UP TO 2x50 POS

mat'l. code		surface		tolerance		projection		product family	
SEE NOTES		ISO 192		ISO 46 ISO 70				DX VCC DR	
lit entry	date	Invariance unless otherwise specified						title	
J 711-004 J00	12.02.22	angles		40.3		mm		KINKED	
K - B19123	14.10.20	linear				scale 10:1		LEGS	
E - F06-0133	06.02.27	D LERNAND		04.11.17				sheet 1 of 1	
F - F06-0204	06.06.20	P NIZZI		04.11.17				dwg no	
G - F07-0194	07.05.31	D LERNAND		04.11.17				71998	
H - F07-0277	14.01.26	uppd P NIZ		04.11.17				A2	
sheet	revision							CUSTOMER	
index	sheet							Drawing	