

NOTES:

① MAT'L: COPPER

PLATING: ELECTRO-TIN (.0003 MIN.)


STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

WIRE SIZE: 22-18 AWG
.25-1.5 MM²



PART NUMBER	"W"	"C"	"L"	"ID"	AVAILABLE STUD SIZES	STOCK THICKNESS
	$\pm .010$	MIN.	MAX.	MIN.		
AA-134-	$\frac{.291}{7.39}$	$\frac{.207}{5.26}$	$\frac{.560}{14.22}$	$\frac{.062}{1.57}$	04, 06, 08	$\frac{.028 \pm .001}{.71}$
AA-138-	$\frac{.245}{6.23}$	$\frac{.207}{5.26}$	$\frac{.560}{14.22}$	$\frac{.062}{1.57}$	04, 06	$\frac{.028 \pm .001}{.71}$
AA-191-	$\frac{.420}{10.67}$	$\frac{.235}{5.97}$	$\frac{.640}{16.26}$	$\frac{.054}{1.37}$	06, 08, 10	$\frac{.031 \pm .001}{.79}$
AA-194-	$\frac{.375}{9.53}$	$\frac{.235}{5.97}$	$\frac{.643}{16.33}$	$\frac{.054}{1.37}$	06, 08, 10	$\frac{.031 \pm .001}{.79}$
AA-197-	$\frac{.325}{8.26}$	$\frac{.235}{5.97}$	$\frac{.640}{16.26}$	$\frac{.054}{1.37}$	04, 06, 08	$\frac{.031 \pm .001}{.79}$
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED REFERENCE SCALE: NTS DATE TITLE: FRAC. DEC. ANG. CHKD. BY: APPRD. BY: DWG. NO. CUSTOMER DWG.						
	$\pm$	$\pm$	$\pm$	$\pm$	SPADE TONGUE TERMINAL KRIMPITE 100-SERIES	EIC INCORPORATED molex
					DRAWN BY: JJ 10-17-84	
					CHKD. BY: GZ 10-22-84	