





RECOMMENDED PCB LAYOUT

SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
DN	DN	DN	
2-3,5-6	2-3,5-4	2-1,5-4	

() = Momentary





CIRCUIT: DPDT 3-WAY

NOTE: JUMPER PIN 3 TO PIN 5


NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 0.4(VA) Max. @20V (AC or DC)
5. FIXED TERM. & MOVING CONTACT: Copper Alloy
6. ELECTRIC LIFE: 50,000 make-and-break cycles
at full load.
w/Gold Plate over Ni plate.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C



SECTION A-A

BRACKET NOT SHOWN



E-SWITCH®

TITLE			
100 DP-7 T1 B4 VS2 R E			
A	12526	RELEASED	10/28/02 CJB
REV.	ECN NO.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSMITTED			
SCALE			
2:1			
DATE			
10/28/02			
DR			
CJB			
DWG			
T121736			
REV			
A			