



	—	8.33[.328]	5/16	63.75[2.51]	12.45[.49]	10.18[.401]	BODY: COPPER ASTM—B187 ANNEALED TIN PL PER MIL—T—10727 0.00381[.000150] MIN THK	277151—7
OBSOLETE	—	13.08[.515]	1/2	69.34[2.73]	16.76[.66]	11.38[.448]		277151—6
	57.0 ±5 GRAMS	6.73[.265]	1/4					277151—5
OBSOLETE	—	13.08[.515]	1/2	63.75[2.51]	12.45[.49]	10.18[.401]	INSERT & FUNNEL: BRASS ASTM B36	277151—4
	54.0 ±5 GRAMS	6.73[.265]	1/4				NICKEL PL SAE AMS QQ—N—290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277151—3
	56.0 ±5 GRAMS	9.91[.390]	3/8				69.34[2.73]	16.76[.66]
	53.0 ±5 GRAMS			63.75[2.51]	12.45[.49]	10.18[.401]	277151—1	
	WEIGHT	’A’	’B’	’L’	’C’	’H’	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 6/23/89 CHK DK SCHRUM MS FEHER 10/16/90		 TE Connectivity			
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM 55.5mm2 [1/0] ALUMINUM 34.3mm2 [2] COPPER			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -					
MATERIAL		FINISH					
SEE TABLE		SEE TABLE		WEIGHT SEE TABLE A2 00779		DRAWING NO C-277151	
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 1	
				REV		R	