

AC Filter for PCB Mounting in Flat Aluminum Housing



Approvals and Compliances

Description

- Line filter in standard and medical version
- 1-stage
- standard attenuation

Characteristics

- Aluminum case provides good shielding
- Designed for standard applications
- Protection against interference voltage from the mains
- Possible interferences generated in the equipment are strongly attenuated
- Universal line filter for standard applications
- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Medical version M80

References

Alternative: Standard version

Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#), [Microsite](#)

Technical Data

Ratings IEC	2 - 16A @ Ta 40 °C / 250VAC; 50Hz
Ratings UL/CSA	2 - 16A @ Ta 40 °C / 125VAC; 60Hz
Leakage Current	standard < 0.5 mA (250V / 60Hz)
Dielectric Strength	> 1.7 kVDC between L-N > 2.7 kVDC between L/N-PE Test voltage (2 sec)
Allowable Operation Temperature	-25 °C to 100 °C
Climatic Category	25/100/21 acc. to IEC 60068-1
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	For PCB mounting, tin-plated
Material: Housing	Aluminum

Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8
MTBF	Technical Details > 200'000h acc. to MIL-HB-217 F

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: FMAB

Approval Logo	Certificates	Certification Body	Description
	VDE Approvals	VDE	Certificate Number: 40004673
	UL Approvals	UL	UL File Number: E72928

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
IEC	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
IEC	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
UL	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
UL	Designed according to	UL 1283	Electromagnetic interference filters
CSA Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
IEC	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.
IEC	Designed for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
China RoHS	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
Medical Equipment	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1


Dimension [mm]

Case 72



Diagrams

Standard version




1) Line
 2) Load

Attenuation Loss


Standard version

- - - 50Ω differential mode 50Ω common mode


2 A




4 A




6 A



10 A




16 A




Medical version (M5)


2 A




4 A




6 A



10 A




16 A




Medical version (M80)


2 A




4 A




6 A



10 A



16 A

**All Variants**

Rated Current [A]	Filter-Type	L [mH]	Cx (X2) [nF]	Cy (Y2) [nF]	R [MΩ]	Weight [g]	Housings	Order Number
2	Standard Version	2 x 8	100	4.7	1	114g	72	5500.2021
4	Standard Version	2 x 3.5	100	4.7	1	114g	72	5500.2022
6	Standard Version	2 x 1.8	100	4.7	1	115g	72	5500.2023
10	Standard Version	2 x 0.82	100	4.7	1	115g	72	5500.2024
16	Standard Version	2 x 0.65	100	4.7	1	115g	72	5500.2025
2	Medical Version (M5)	2 x 8	100	-	1	114g	72	5500.2106
4	Medical Version (M5)	2 x 3.5	100	-	1	114g	72	5500.2107
6	Medical Version (M5)	2 x 1.8	100	-	1	115g	72	5500.2108
10	Medical Version (M5)	2 x 0.82	100	-	1	115g	72	5500.2109
16	Medical Version (M5)	2 x 0.65	100	-	1	115g	72	5500.2110
2	Medical Version (M80)	-	-	-	-	114g	72	5500.2111
4	Medical Version (M80)	-	-	-	-	114g	72	5500.2112
6	Medical Version (M80)	-	-	-	-	115g	72	5500.2113
10	Medical Version (M80)	-	-	-	-	115g	72	5500.2114
16	Medical Version (M80)	-	-	-	-	115g	72	5500.2115

Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>**Packaging unit**

10 Pcs