



NOTES:

1. MATERIAL: ANNEALED HIGH CONDUCTIVITY COPPER.
TIN PLATED
2. FOR USE WITH COPPER OR TIN PLATED COPPER
CONDUCTORS ONLY.
3. ACCOMODATES CODE CABLE, SOLID WIRE (WHERE NOTED),
FLEX LOCOMOTIVE (DLO), AND FLEX CLASSES G, H, & I.
4. ANY SINGLE TAP OR COMBINATION OF TAPS MAY BE
USED IN CONJUNCTION WITH MAIN WIRE PORT.
5. UL LISTED AND CSA CERTIFIED FOR APPLICATIONS
UP TO 600V. TEMPERATURE RATING 90° C MAX.
6. FLAME RETARDANT CABLE TIES
(UL94 V-0 RATED NYLON WITH L.O.I. =28 MIN.)
ARE PROVIDED WITH THE TAPS TO RETAIN THE WIRES
IN POSITION FOR CRIMPING.
7. TO ORDER H-TAP WITH INSULATING COVERS SEE PART
NUMBERS IN TABLE.
8. H-TAPS AND KITS ARE PACKAGED INDIVIDUALLY.
(-1 PACKAGING CODE)
9. FOR PANDUIT CLEAR INSULATING COVER USED WITH HTAP,
ORDER PANDUIT PART NO. CLRCVR6-1.

LISTED
WIRE CONNECTOR

CERTIFIED

H-TAP PART NUMBER	H-TAP & CLEAR COVER KIT PART NUMBER	COPPER CONDUCTOR SIZES CODE WIRE (FLEX WIRE)				WIRE STRIP LENGTH (in.)	CRIMP DIE COLOR CODE	PANDUIT INSTALLATION TOOLS
		MAIN	TAP 1	TAP 2	TAP 3			CT-940CH CT-2940 CRIMP DIE NO/DIE INDEX NO. (# OF CRIMPS=1)
HTCT750-4/0-1	HTWC750-4/0-1	750-350 (550-500)	4/0-1/0 (250-1/0)	1-6 STR/SOL (1-8)	2-14 (2-14)	1-3/8	YELLOW	CD-940H-750 PH75

C41384_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

01	02/04	RWK		ADDED NOTE 9.				HTCT750-4/0 H-TAP COPPER COMPRESSION CONNECTOR			
00	11/03	KLFU	RLS	DRAWING RELEASED	11144	LSM	JAC				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								KLFU		NONE	C41384