





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC []


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



**SUGGESTED
MOUNTING PATTERN**

1. INDUCTANCE TO BE 0.1 H MINIMUM.
2. PACKAGE: BULK OR BLISTER TAPE TO IEC-60286-3 TYPE II AND EIA-481-A.
3. TUSONIX STANDARD PART NUMBER: 4700-003.
TUSONIX RoHS COMPLIANT PART NUMBER:
4700-003 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS
PART NUMBER WHEN ORDERING.
4. PART MARKING: STANDARD PART: NO MARKING.
RoHS PART: LABELED ON PACKAGING ONLY.
5. ELECTRODE TERMINATION: STANDARD 60/40
SOLDER; RoHS COMPLIANT - MATTE TIN.

CAP.		TOLERANCE	WVDC		TEST VOLTAGE	I.R.MIN. @ 100 (VDC.)	IDC	TYPICAL NO LOAD INSERTION LOSS dB AT 25°C PER MIL-STD-220		
			85°C	+125°C				10 MHZ	100 MHZ	1 GHZ
2000 pF		GMV	100	100	300 VDC	10 G	10 A	10	45	70

REVISION RECORD	Original Release C.O. 941020-1	ADDED DC COLUMN E.C 10-26-94	REISSUE 941020-1 DIM. .230 WAS .238 E.C. 11-16-94	REISSUE 941020-1 REVISED DWG. ORIENTATION SYMBOL & 1.R. MIN.@ 100 (VDC) ADDED S.M. 02-13-03	20030213-1-12 REVISED DRAWING; S.M. 06-20-03	20030619-2-01 ADDED NOTES 3,4 & 5. S.M. 06-10-05	20050607-5-02	--TOLERANCES-- Unless Otherwise Specified			Title SURFACE MOUNT SQUARE STYLE PI FILTER
	DECIMAL ± .005 [0.13]										
	ANGLES ± 							Drawn FG 9-9-94		Scale 7 X	
	TUSONIX TUCSON, ARIZONA							Approved NV 9-9-94			
								A	4700-003		