






MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4100-053.
TUSONIX RoHS COMPLIANT PART NUMBER: 4100-053 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- PART MARKING: STANDARD PART: NO MARKING.
RoHS PART: GREEN INK DOT ON INSULATION BAND.

Cx 1KHz @ 25°C	WORKING VOLTAGE		IR	CURRENT Idc (A)	TYPICAL NO LOAD INSERTION LOSS @ 25°C (dB) PER MIL-STD-220			
	+85°C 250 @ 60 Hz VAC	+125°C 200 VDC			1 MHz	10 MHz	100 MHz	1 GHz
10,000/5,000			10 G	10 MAX.	2	18	60	70

X-2015 Rev-0	REVISION RECORD					--TOLERANCES-- Unless Otherwise Specified	Title P.C. BOARD MOUNT TYPE LOW PASS FILTER		
	Original Release C.O.	0	WAS SK 6871-001. EC 07-27-88						
	4056	1	COMPLETELY REVISED & REDRAWN PER SK 6905-000. L.E. 09-29-88						
	4170	2	DIM. REVISED .200 WAS .175. L.E. 11-10-89						
	4900	3	RDN TO COMP FMT. S.M. 05-09-00						
	20000508-2-01	4	ADDED NOTES 1-3. S.M. 05-24-05						
	20050513-2-02	5							
						DECIMAL ± .031 [0.79]	Drawn S.M. 05-08-00		Scale 4 X
						ANGLES ± 	Approved T.C. 05-08-00		
						TUSONIX TUCSON, ARIZONA	A	4100-053	