




PANDUIT PART NO.*	BUNDLE DIA.		A	B	C	D	E	F	G	RECOMMENDED STUD SIZE		MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)								STUD	LENGTH			
PLST30SC	.24 (6)	1.18 (30)	.050 (1.3)	.19 (4.8)	1.45 (36.8)	.41 (10.4)	.32 (8.1)	5.74 (146)	.41 (10.4)	10-24 (5)	.375 (9)	50 (222)	STANDARD	.36 (163)
PLST50SC	.24 (6)	1.97 (50)	.050 (1.3)	.19 (4.8)	1.45 (36.8)	.41 (10.4)	.32 (8.1)	8.14 (207)	.41 (10.4)	10-24 (5)	.375 (9)	50 (222)	STANDARD	.44 (200)

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2) THIS PART IS RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

LOCKING STUD MOUNT CABLE TIE
PLST__SC SERIESUNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1 (.25) (.XXX) ± .020 (.51)
(.XX) ± .02 (.5) ANGLES ± ----UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.CHANGED FORMAT FOR CONSISTENCY,
REARRANGED DIM LETTERS, ADDED TOLERANCECORRECTED MIN LOOP TENSILE METRIC
CONVERSION

26443 8

DRAWN BY
CDHDATE
08/09/91CHK'D
HVPMAT'L:
-30
HEAT STABILIZED
BLACKSCALE
NONEDRAWING NO.
SS-26443DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
-----	------	----	-----	-------------	-----	---	------	-----