

SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!			

Material

- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
Solid wire(AWG): 14-24
Stranded wire(AWG): 14-24
- Torque(Lb-In): 3.2Lb-in
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

RoHS Compliant

PART NUMBER:

OSTT9XX2180

No. of Poles

02: 2 Poles

03: 3 Poles





... ..

24 24 Poles

COLOR

5: Green

8: Grey (Standard)



N=Number of poles

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

OST ON-SHORE TECHNOLOGY, INC.

TITLE		OSTT9 - 5.08mm Series	
PART NO.	OSTT9XX2180	DWG NO.	OSTT9XX2180.DWG
APPROVED	Shi Jun 2006.10.19	CHECKED	Shi Jun 2006.10.19
DESIGNED	xionghaitao 2006.10.19	DRAWN	xionghaitao 2006.10.19
CUST NO.		Tolerance	
		UNIT: mm	X. ±0.50
		SCALE: NONE	X.X ±0.30
		REV: C	X.XX ±0.10
SHEET: 01/01		X° ±1°	