



# SPECIFICATION

(Reference sheet)

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor


- Samsung P/N : CL31C151JIFNNNE
- Description : CAP, 150pF, 1000V, ± 5%, C0G, 1206

## A. Samsung Part Number

CL 31 C 151 J I F N N E  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	1206 (inch code)	L: $3.20 \pm 0.15$ mm	W: $1.60 \pm 0.15$ mm
③ Dielectric	C0G	⑧ Inner electrode	Ni
④ Capacitance	150 pF	Termination	Cu
⑤ Capacitance tolerance	± 5%	Plating	Sn 100% (Pb Free)
⑥ Rated Voltage	1000 V	⑨ Product	Normal
⑦ Thickness	$1.25 \pm 0.15$ mm	⑩ Special	Reserved for future use
		⑪ Packaging	Embossed Type, 7" reel

## B. Structure and dimension



Samsung P/N (Lead Free)	Dimension(mm)			
	L	W	T	BW
CL31C151JIFNNNE	$3.20 \pm 0.15$	$1.60 \pm 0.15$	$1.25 \pm 0.15$	$0.50 \pm 0.30$

### C. Samsung Reliability Test and Judgement condition

	Performance	Test condition
<b>Capacitance</b>	Within specified tolerance	$1\text{MHz} \pm 10\%$ / 0.5~5Vrms
<b>Q</b>	1,000 min	
<b>Insulation Resistance</b>	10,000Mohm or $500\text{Mohm} \times \mu\text{F}$ Whichever is smaller	$500 \pm 50 \text{ Vdc}$ 60±5 sec.
<b>Appearance</b>	No abnormal exterior appearance	Microscop (X10)
<b>Withstanding Voltage</b>	No dielectric breakdown or mechanical breakdown	120% of the rated voltage
<b>Temperature Characteristics</b>	C0G (From -55°C to 125°C, Capacitance change should be within ±30PPM/°C)	
<b>Adhesive Strength of Termination</b>	No peeling shall be occur on the terminal electrode	$500\text{g} \times \text{F}$ , for 10±1 sec.
<b>Bending Strength</b>	Capacitance change : within ±5% or ±0.5pF whichever is larger	Bending to the limit (1mm) with 1.0mm/sec.
<b>Solderability</b>	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder $245 \pm 5^\circ\text{C}$ , 3±0.3sec. (preheating : 80~120 °C for 10~30sec.)
<b>Resistance to Soldering heat</b>	Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec.	Solder pot : $270 \pm 5^\circ\text{C}$ , 10±1sec.
<b>Vibration Test</b>	Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours ' 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within ±7.5% or ±0.75pF whichever is larger Q : 200 min IR : 500Mohm or $25\text{Mohm} \times \mu\text{F}$ Whichever is smaller	With rated voltage $40 \pm 2^\circ\text{C}$ , 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within ±3% or ±0.3pF whichever is larger Q : 350 min IR : 1,000Mohm or $50\text{Mohm} \times \mu\text{F}$ Whichever is smaller	With 100% of the rated voltage Max. operating temperature 1000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec.	1 cycle condition Min. operating temperature → 25°C → Max. operating temperature → 25°C  5 cycle test

※ The reliability test condition can be replaced by the corresponding accelerated test condition.

### D. Recommended Soldering method :

Reflow ( Reflow Peak Temperature :  $260 \pm 0/-5^\circ\text{C}$ , 10sec. Max )

 Product specifications included in the specifications are effective as of March 1, 2013.

Please be advised that they are standard product specifications for reference only.

We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications,  
please contact our sales personnel or application engineers.

## **- Disclaimer & Limitation of Use and Application -**

*The products listed in this Specification sheet are **NOT** designed and manufactured for any use and applications set forth below.*

*Please note that any misuse of the products deviating from products specifications or information provided in this Spec sheet may cause serious property damages or personal injury.*

*We will **NOT** be liable for any damages resulting from any misuse of the products, specifically including using the products for high reliability applications as listed below.*

*If you have any questions regarding this 'Limitation of Use and Application', you should first contact our sales personnel or application engineers.*

- ① Aerospace/Aviation equipment*
- ② Automotive or Transportation equipment (vehicles, trains, ships, etc)*
- ③ Medical equipment*
- ④ Military equipment*
- ⑤ Disaster prevention/crime prevention equipment*
- ⑥ Any other applications with the same as or similar complexity or reliability to the applications set forth above.*