





PRODUCT NO.
SEE SHEET 4

- NOTE
1. PRODUCT SPEC. : GS-12-195
 2. PACKAGING SPEC. : GS-14-786
 3. MATERIAL:
1) HOUSING : LCP, UL94V-0, COLOR BLACK
2) CONTACT : COPPER ALLOY
3) HOLD DOWN : BRASS
 4. FINISH
1) TERMINAL : SEE TABLE
2) HOLD DOWN : SEE TABLE
 5. CO-PLANARITY : 0.1 MAX.(INCLUDE HOLD DOWN)
 6. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDER APPLICATION.

rev	ecn no	dr	date
A	DG11-0085	SH	2011-03-29
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface	tolerance std	projection	MM	
			ASME Y14.5	ASME Y14.5			
			TOLERANCES UNLESS OTHERWISE SPECIFIED			size	Scale
Dr	SH MIAO	2011-03-29	ANGULAR	0.X	±0.30	A2	1:1
Eng	SH MIAO	2011-03-29		0.XX	±0.15		
Chr	RICK BIAN	2011-03-29	0° ±2°	0.XXX	±0.08	ECN	DG11-0085
Appr	HSIA JOSEPH	2011-03-29	Product family			Spec ref	RELEASED
			Product family			SO-DIMM	
			Product family			DDR SO-DIMM 0.6mm PITCH 200 POS	
			Product family			STANDARD TYPE ASS'Y	
			Product family			10117867C	
			Product family			Rev.	A
			Product family			Customer COPY	sheet 1 of 4






PRODUCT NO.
10117867-x52xx

RECOMMENDED MOUNTING P.C.B LAYOUT

Copyright FCI.
FCI

FCI	DDR SO-DIMM 0.6mm PITCH 200 POS		diag no	10117867C	Rev.
	STANDARD TYPE ASS'Y				A
	catalog no	-	CUSTOMER COPY	sheet 2 of 4	



Technical drawing of a detail Y, showing a cross-section of a mechanical part. The drawing includes the following dimensions and features:

- Overall width: 4
- Top radius: R0.5
- Left side height: 4.0 ± 0.1
- Internal step height: 2.55
- Right side height: 4.2
- Bottom width: 1.0 ± 0.1
- Feature control frame for a hole: $\varnothing 0.1$ A B C
- Feature control frame for a hole: 0.45 ± 0.03
- Feature control frame for a hole: MAX 0.25
- Feature control frame for a hole: A

DETAIL Y
SCALE 10:1

1		2		3		4		5		6		7		8	
PRODUCT NO.		LOCATING PEG		TERMINAL CONTACT AREA FINISH		HOLD DOWN FINISH		SOLDER TAIL FINISH							
A	10117867-052FS	YES		Au FLASH		Pure Sn PLATING		Au FLASH PLATING		10117867- LF <					