

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

WE-2R058-A41**WE-2R058-A41**

PAGE 1 OF 1

MDRAWING
NUMBER

10

ISSUE

REPLACES

RELEASE NO. PR-93

CHECK

REVISIONS

A	CO31019 CO31188	SRH	11 SEP 72
B	CO32144	GLH	27 JUL 73
C	CO33356	RER	25 APR 74
D	CO36627	CJH	8 APR 76
E	CO38423	CEB	22 MAR 77
F	CO39564	SLB	2 MAR 78
G	CO58782	WJM	25 JAN 86
H	CO79125	SAD	DEC 94
J	204993	GJW	11 MAR 02

CHECK

13 FEB 68


LSD

CHECK

RE R 12 FEB 68

FO-80376

DRAWN



NOTE -

△ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA
ON 1.000 ± .002 CENTERS

2- PLASTIC MATERIAL USED:

CASE - - - DUREZ 16274 OR EQUIVALENT (NORMALIZED)

COVER - - - GE12983 OR EQUIVALENT (NORMALIZED)

PLUNGER - - GE EF-4530 OR EQUIVALENT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 24 OZ MAX

RELEASE FORCE - - - - - 10 OZ MIN

DIFFERENTIAL TRAVEL - - - - .005 MAX

OVERTRAVEL - - - - - .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C25-A-125, 250, 480 VAC 1 HP-125 VAC;
2 HP-250 OR 480 VAC; PILOT DUTY
750 VA-480 VAC, MAX; 60/75°C (Cu)

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .063 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[WE-2R058-A41](#)