

STATIC SHIELDING BAGS
TYPE 6S1-.... and STS 909 (Flat and reclosable)

Electrical properties (typical values)


Surface Resistivity		
Interior	ASTM D257, EIA 541	$10^9 - 10^{10}$ Ohm / sq
Metal	ASTM D257, EIA 541	100 Ohm / sq
Exterior	ASTM D257, EIA 541	$10^9 - 10^{10}$ Ohm / sq
Static shielding	MIL-B-81705C, EIA 541	< 30 V
	EOS/ESD S11.31	< 10 nJ
Static decay	MIL-B81705C, FTMS 101 MTH 4046	< 0,5 sec.
Charge generation	Teflon	0.09 nC/sq.in.
	Quartz	0.01 nC/sq.in.

Physical Properties (Typical values)

Tensile strength	ASTM D882	> 25 lb
Seam strength	MIL-B-81705C	pass
Light transmission		40%
Heat sealing conditions	Temperature	120-190°C
	Time	0,5 -3,5 sec.
	Pressure	30 -70 PSI
Thickness		3,1 mils
Outgassing	ASTM E595	pass
Non-corrosive	FTMS101, MTH 3005	pass

Structure: (Film)

Outside



Inside

Bags meets or exceeds: MIL-B-81705C Type III, EIA 541, EIA 625, MIL-HDBK-263, MIL-STD-1686, EOS/ESD Standards, EN100015/1 / IEC 61340-5-1

The information set forth herein is intended for use by persons having technical skill at their own discretion and risk. Since conditions of use are outside our control, we make no warranties, express or implied and assume no liability in connection with any use of this information.