

# LTC3588EMSE-1

## Piezoelectric Energy Harvesting Power Supply

### DESCRIPTION

Demonstration Circuit 1459A is an energy harvesting power supply featuring the LTC3588-1. The LTC3588-1 integrates a low-loss full-wave bridge with a high efficiency buck converter to form a complete energy harvesting solution optimized for high output impedance energy sources such as piezoelectric transducers. An ultralow quiescent current undervoltage lock-out mode with a wide hysteresis window allows charge to accumulate on an input capacitor until the buck converter can efficiently transfer a portion of the stored charge to the output. Four output voltages are pin selectable with up to 100mA of continuous output

current. A power good comparator produces a logic high referenced to VOUT on the PGOOD pin when the converter reaches the programmed VOUT, signaling that the output is in regulation.

The LTC3588EMSE-1 is available in a 10-lead (3mm × 2mm) MSE surface mount package with exposed pad.

LT, LTC, LTM, LT, Burst Mode, OPTI-LOOP, Over-The-Top and PolyPhase are registered trademarks of Linear Technology Corporation. Adaptive Power, C-Load, DirectSense, Easy Drive, FilterCAD, Hot Swap, LinearView,  $\mu$ Module, Micropower SwitcherCAD, Multimode Dimming, No Latency  $\Delta\Sigma$ , No Latency Delta-Sigma, No  $R_{SENSE}$ , Operational Filter, PanelProtect, PowerPath, PowerSOT, SmartStart, SoftSpan, Stage Shedding, SwitcherCAD, ThinSOT, UltraFast and VLDO are trademarks of Linear Technology Corporation. Other product names may be trademarks of the companies that manufacture the products.

**TABLE 1**  
**PERFORMANCE SUMMARY** Specifications are at  $T_A = 25^\circ\text{C}$

| SYMBOL    | PARAMETER            | CONDITIONS   | MIN   | MAX      | UNITS |
|-----------|----------------------|--------------|-------|----------|-------|
| VIN       | Input Voltage Range  |              |       | 18.0     | V     |
| VOUT 1.8V | Output Voltage Range | D0 = 0, D1=0 | 1.71  | to 1.89  | V     |
| VOUT 2.5V | Output Voltage Range | D0 = 1, D1=0 | 2.425 | to 2.575 | V     |
| VOUT 3.3V | Output Voltage Range | D0 = 0, D1=1 | 3.201 | to 3.399 | V     |
| VOUT 3.6V | Output Voltage Range | D0 = 1, D1=1 | 3.491 | to 3.708 | V     |

### OPERATING PRINCIPLE

Refer to the block diagram within the LTC3588-1 data sheet for its operating principle.

The LTC3588-1 is an ultralow quiescent current power supply designed specifically for energy harvesting and/or low current step-down applications. The part is designed to interface directly to a piezoelectric or alternative A/C energy source, rectify and store the harvested energy on an external capacitor, bleed off any excess energy via an internal shunt

regulator, and maintain a regulated output voltage by means of a nano-power high efficiency synchronous buck regulator.

The LTC3588-1 has an internal full-wave bridge rectifier accessible via PZ1 and PZ2 that rectifies AC inputs such as those from a piezoelectric element. The rectified output is stored on a capacitor at the VIN pin and can be used as an energy reservoir for the buck converter. The bridge is capable of carrying up to 50mA.



while monitoring the input current. If the current remains less than 5mA, increase PS1 until output turns on. Verify input voltage, VIN, UVLO of 3.77V to 4.30V.

4. Increase PS1 to 12V and set LOAD1 to 100mA. Verify voltage on VOUT is within the VOUT 1.8V range in Table 1. Verify that the output ripple voltage is between 40mV and 70mV. Verify that PGOOD is high (VOUT). Decrease LOAD1 to 5mA.
5. Decrease PS1 to 0V and move the connection for PS1 from VIN to PZ1. Slowly increase PS1 voltage to 2.0V while monitoring the input current. If the current remains less than 5mA, increase PS1 to 12V. Verify voltage on VOUT is within the VOUT 1.8V range in Table 1. Decrease PS1 to 0V, swap the PZ1 move the lead connections to PZ2 and repeat the test. Decrease PS1 to 0V and move the connection for PS1 from PZ2 to VIN.
6. Set JP1 to 1. Increase PS1 to 12V and set LOAD1 to 100mA. Verify voltage on VOUT is within the VOUT 2.5V range in Table 1. Verify that the output ripple voltage is between 40mV to 70mV.
7. Set JP1 to 0 and JP2 to 1. Set LOAD1 to 100mA. Verify voltage on VOUT is within the VOUT 3.3V range in Table 1. Verify that the output ripple voltage is between 50mV and 80mV.
8. Set JP1 to 1 and JP2 to 1. Set LOAD1 to 100mA. Verify voltage on VOUT is within the VOUT 3.6V range in Table 1. Verify that the output ripple voltage is between 60mV and 90mV.
9. Increase PS1 to 18V and set LOAD1 to 100mA. Verify voltage on VOUT is within the VOUT 3.6V range in Table 1. Verify that the output ripple voltage is between 60mV and 90mV.
10. Decrease LOAD1 to 1mA. Turn off PS1 and insert a 1K ohm resistor between the positive lead of the PS1 and the VIN turret. Turn on PS1 and while monitoring the voltage on VIN, increase PS1 until the voltage on VIN is 3V below the voltage on PS1. Verify input voltage, VIN,  $V_{SHUNT}$  of 19.0V to 21.0V.
11. Turn off PS1 and LOAD1.




Figure 1. Proper Measurement Equipment Setup



| Item                                             | Qty | Reference - Des   | Part Description                          | Manufacturer, Part #         |
|--------------------------------------------------|-----|-------------------|-------------------------------------------|------------------------------|
| <b>REQUIRED CIRCUIT COMPONENTS:</b>              |     |                   |                                           |                              |
| 1                                                | 1   | C1                | CAP, CHIP, X5R, 22uF, 10%, 25V, 1210      | AVX, 12103D226KAT1A          |
| 2                                                | 1   | C3                | CAP, CHIP, X5R, 1uF, 10%, 6.3V, 0402      | TDK, C1005X5R0J105KT         |
| 3                                                | 1   | C4                | CAP, CHIP, X5R, 4.7uF, 10%, 6.3V, 0603    | TDK, C1608X5R0J475KT         |
| 4                                                | 1   | C5                | CAP, CHIP, X5R, 100uF, 20%, 6.3V, 1206    | Taiyo Yuden, JMK316BJ107ML-T |
| 5                                                | 1   | L1                | INDUCTOR, 10uH, 0.43A, 180mΩ, 3mm x 3mm   | Sumida, CDRH2D18/LDNP-100N   |
| 6                                                | 1   | U1                | Piezoelectric Generator Power Supply      | Linear Tech., LTC3588EMSE-1  |
| <b>ADDITIONAL DEMO BOARD CIRCUIT COMPONENTS:</b> |     |                   |                                           |                              |
| 1                                                | 0   | C2 (OPT)          | AL ELECT, 100uF, 35V, 20%, 8.2mm x 11.1mm | VISHAY, MAL291355101E3       |
| 2                                                | 0   | C6 (OPT)          | SUPERCAP, 3.0F, 2.7V, 8mm x 20mm          | NESS, ESHSR-0003C0-002R7     |
| 3                                                | 0   | C7 (OPT)          | SUPERCAP, 0.43F, 5.5V, 20mm x 18mm        | CAP-XX, HA230F               |
| 4                                                | 0   | R1,R2 (OPT)       | RES., CHIP, 249K, 1/16W, 1%, 0402         | VISHAY, CRCW0402249KFKED     |
| <b>HARDWARE FOR DEMO BOARD ONLY:</b>             |     |                   |                                           |                              |
| 1                                                | 6   | E1,E2,E3,E4,E5,E6 | TURRET, 0.09 DIA                          | MILL-MAX, 2501-2             |
| 2                                                | 2   | E7,E8             | TURRET, 0.061 DIA                         | MILL-MAX, 2308-2             |
| 3                                                | 2   | JP1,JP2           | HEADER, 3 PINS, 2mm                       | SAMTEC, TMM-103-02-L-S       |
| 4                                                | 2   | JP1,JP2           | SHUNT, 2MM                                | SAMTEC, 2SN-BK-G             |

Bill of Materials