

NOTES:


1. ROHS COMPLIANT
2. MATERIAL:
 - PANEL CONNECTOR - POLYPROPYLENE, UL RATING 94-HB
 - HEADER CONNECTOR - POLYESTER, UL RATING 94-V0
 - LENS - POLYCARBONATE - UL RATING 94-V2
 - MOISTURE SEAL - EPDM
 - RING - THERMOPLASTIC
 - TERMINALS - PHOSPHOR BRONZE, TIN PLATE
 - WIRE - 24 AWG 1007/1569
3. MOUNTING: HOLE SIZE .281" (7.2mm) OPENING ON 3/8" CENTERS (9.52mm)
4. PANEL THICKNESS: .030" (0.76mm) MIN TO .125" (3.18mm) MAX
 - FOR PANEL THICKNESS .030" (0.76mm) TO .045" (1.14mm) USE TWO (2) SPC 060 SPACERS
 - FOR PANEL THICKNESS .050" (1.27mm) TO .100" (2.54mm) USE ONE (1) SPC 060 SPACER
 - FOR PANEL THICKNESS .105" (2.67mm) TO .125" (3.18mm) NO SPACER REQUIRED
5. LED LEAD LENGTH:
 - FOR CMC 285 - .350" $\pm$.010 (8.89mm $\pm$ 0.25)
 - FOR CMC 313, CMC 321, CMC 323, AND CMS 322 - .220" $\pm$.010 (5.59mm $\pm$ 0.25)
6. FOR STANDARD DRY APPLICATIONS USE CMC 285, CMC 313, CMC 321 OR CMC 323; FOR WET OR DRY APPLICATIONS USE CMS 322 (MEETS NEMA4/ IP56)
7. ALSO CAN BE ORDERED CNX 310 XXX FOR CONNECTOR AND RESISTOR ONLY
8. U.S AND FOREIGN PATENT ISSUED

REVISIONS				
ECN #	REV	DESCRIPTION	DATE	INITIALS
	001	REVISED PER ECR 111009A201	2/22/11	KH

CABLE ORDERING CODE EXAMPLE:
CNX 310 056 E 4 1 08

* CALL FACTORY FOR
ADDITIONAL OPTIONS

LED & SPACER
(ORDER SEPERATELY)




5MM LED




SPC 060

RESISTOR *		TERMINATION *		WIRE SIZE *		WIRE COLOR *		WIRE LENGTH *	
000 =	NO RESISTOR	X =	STRIPPED END	4 =	24 AWG	1 =	WHITE - BLACK	04 =	4 INCHES (101.6mm)
012 =	120 OHMS	E =	SINGLE ROW LOCKING HEADER			2 =	RED - BLACK	06 =	6 INCHES (152.4mm)
018 =	180 OHMS	G =	SINGLE ROW PLAIN HEADER					08 =	8 INCHES (203.2mm)
033 =	330 OHMS							12 =	12 INCHES (304.8mm)
056 =	560 OHMS							18 =	18 INCHES (457.2mm)
120 =	1200 OHMS							24 =	24 INCHES (609.6mm)
220 =	2200 OHMS								

LENS
(ORDER SEPERATELY)




CMC 285



CMC 313
CMC 321
CMC 323



CMS 322



DIMENSION STYLE: INCHES / MM GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL		VCC OPTOELECTRONICS 190 BOSSTICK BLVD, SUITE 101 SAN MARCOS, CA 92069 U.S.A PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vcclite.com	
INCHES ±.500 MM ± 12.7		SEE NOTES			
 THIRD ANGLE PROJECTION		FINISH		TITLE:	
PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC. IS PROHIBITED.		SEE NOTES		CNX 310 XXX CABLE ASSEMBLY	
		APPROVAL		DATE	
		DRAWN K.Howard		2/22/11	
		CHECKED AZ		2/22/11	
		DO NOT SCALE DRAWING			
		SIZE		DWG. NO.	
		B		CNX 310 XXX ASSY	
		SCALE: 2:1		REV 001	
				SHEET 1 OF 1	