


REV.	DATE	DESCRIPTION
NC	08/11/98	INITIAL RELEASE
A	07/21/05	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex			
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	DRAWN G.R.S.	07/21/05				
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	CHECKED		PART DESCRIPTION			
5	FERRULE	COPPER	GOLD	1		ISSUED		SMA R/A CRIMP PLUG - LMR 200			
4	COVER	BRASS	GOLD	1		SHEET 1 OF 1		-			
3	CONTACT PIN	BRASS	GOLD	1				PART NO.			
2	INSULATOR	TEFLON	NATURAL	1				132235			
1	BODY	BRASS	GOLD	1							
DESCRIPTION MATERIAL FINISH QTY					DO NOT SCALE DRAWING	CAD FILE C:/132/1132235.DWG	DWG. NO. 132235.DWG	REV. A	SIZE A	SCALE NA	