




PRODUCT NO	REMARKS
10038339-001LF	WITHOUT PICK-UP CAP
10038339-001CLF	WITH PICK-UP CAP
10038339-002LF	WITHOUT PICK-UP CAP
10038339-002CLF	WITH PICK-UP CAP




10038339-001LF / -002LF



10038339-001CLF / -002CLF



RECOMMENDED PCB LAYOUT FOR 10038339-001LF & -001CLF



RECOMMENDED PCB LAYOUT FOR 10038339-002LF & -002CLF

NOTES:

1. MATERIAL :
HOUSING : HIGH TEMPERATURE THERMOPLASTIC
CONTACTS : COPPER ALLOY
ESD CONTACTS : COPPER ALLOY
2. PLATING :
CONTACTS : 1.27um/50u" MIN NICKEL UNDERPLATE
0.76um/30u" MIN GOLD AT CONTACT AREA
2.54um/100u" MIN TIN AT SOLDER TAIL
ESD CONTACTS : 1.27um/50u" MIN NICKEL UNDERPLATE
2.54um/100u" MIN TIN AT OVERALL
3. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED ON GS-22-008.


rev	ecn no	dr	date
A	S05-0136	TAY	2005-05-11
B	S05-0216	TAY	2005-08-01
C	S05-0275	TAY	2005-09-22
D	S07-0042	TAY	2007-02-07
E	S10-0071	TAYKP	2010-03-30
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ASME Y14.5		☒	tolerance std ASME Y14.5		projection 		MM 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	KP TAY	2007-02-07	ANGULAR		LINEAR	0.X	±0.35	size	A4			Scale	2:1
Eng	KP TAY	2010-03-30				0.XX	±0.25						
Chr	KP TAY	2010-03-30	0° ±2°			0.XXX	±0.13	ECN			S10-0071		
Appr	JOEY NG	2010-03-30	Product family						Spec ref				-
			file SCA-2 & FIBER CHANNEL RECEPT, SMT				dwg no 10038339				Rev E		
			catalog no				CUSTOMER				sheet 1 of 2		




Copyright FCI.



PRODUCT NO
REFER TO PAGE 1




DETAIL A
SCALE 4:1




TYP 0.42 ± 0.13
 $\oplus 0.30 \text{ L A L}$



SECTION Y-Y



10038339-001LF / -001CLF



10038339-002LF / -002CLF



title SCA-2 & FIBER CHANNEL
RECEPT, SMT
catalog no

dwg no 10038339

Rev. E

CUSTOMER sheet 2 of 2