

SPECIFICATIONS

RoHS Compliant




Model Number: GL24B7

Part Number: 031636

March 29, 2005

Mechanical Drawing:



Motor:

Nominal Voltage	= 24 vdc
Operating Voltage Range	= 12 - 24 vdc
Nominal Running Current	= 0.630 amps
Locked Rotor Current	= 1.350 amps
Running Power	= 15.0 watts
Average Speed	= 3200 RPM
Bearings	= Ball
Air Flow	= 150 CFM
Acoustic	= 53.6 dBA

Construction:

Venturi: Die cast zinc alloy, painted black.
Propeller: Plastic, Black, UL 94V-0.

Life Expectancy:

This fan is designed for continuous duty life of 82,500 hours at 50°C.

Agency Certifications:

UL, CE

Additional Features:

Brushless DC Motor
Locked Rotor Protection
Automatic Restart Capability
Reverse Polarity Protected
Operating Temperature: -10°C to 70°C
Storage Temperature: -40°C to 85°C

Tachometer:

Output: 5vdc TTL
I_c: 5mA Typical
Isolated: No
Pulses per Revolution: 2

Termination:

12" Lead wires, UL 1061, 22 AWG
Red - Power (+)
Black - Ground (-)
Blue/White - Tachometer (Output)