


ELECTRICAL CHARACTERISTICS @ 25°C





1.0 INDUCTANCE:	
(P2-P3)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS
(P4-P5)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS
(P7-P8)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS
(P9-P10)	: 350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS
2.0 TURNS RATIO:	
(P2-P3):(J1-J2)	: 1CT : 1CT ± 2%
(P4-P5):(J3-J6)	: 1CT : 1CT ± 2%
(P7-P8):(J4-J5)	: 1CT : 1CT ± 2%
(P9-P10):(J7-J8)	: 1CT : 1CT ± 2%
3.0 RETURN LOSS: 100 OHM REF.	
500kHz TO 40MHz	: -18dB MIN.
40MHz TO 100MHz	: -12+20LOG(f/80MHz) MIN.
4.0 INSERTION LOSS: RS=RL=100 OHMS	
100kHz TO 100MHz	: -1.2dB MAX.
5.0 CROSS TALK: Ch1-Ch2, Ch1-Ch3, Ch1-Ch4, Ch2-Ch3, Ch2-Ch4, Ch3-Ch4	
1MHz TO 30MHz	: -35dB MIN.
30MHz TO 80MHz	: -24dB MIN.
80MHz TO 100MHz	: -25dB MIN.
6.0 CM TO CM REJECTION:	
100kHz TO 100MHz	: -30dB MIN.
7.0 CM TO DM REJECTION:	
100kHz TO 100MHz	: -35dB MIN.
8.0 VOLTAGE WITHSTAND:	
(J1,J2) TO (P2,P3)	: 1500Vrms
(J3,J6) TO (P4,P5)	: 1500Vrms
(J4,J5) TO (P7,P8)	: 1500Vrms
	: 1500Vrms
9.0 THIS COMPNENT IS A PATENT PRODUCT;US PATENT NUMBER 7,123,117.	



ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.	[] METRIC DIM. AS REFERENCE	
RS Zhang	04-22-10	MagJack® 10/100/1000BT TAB UP SHIELDED PATENTED	SI-51014-F	TOL. IN INCH	UNIT : INCH [mm]	REV. : A1
DRAWN BY	DATE		FILE NAME	.X	SCALE : N/A	SIZE : A4
RS Zhang	04-22-10		SI-51014-F.DWG	.XX		PAGE : 2
				.XXX		

THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

RoHS
2002/95/EC





NOTES:

1. CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACT/SHIELD: COPPER ALLOY
SHIELD PLATING: NICKEL OR TIN
CONTACT PLATING: SELECTIVE GOLD,
50 MICRO-INCHES MIN. IN CONTACT AREA.
2. PIN NOT ELECTRICALLY CONNECTED MAYBE OMITTED.
SEE ELECTRICAL DRAWING FOR OMITTED PINS.
3. TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS.
4. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ± 0.005 [0.13]
5. WAVE SOLDER COMPATIBLE - PREHEAT 125°C/90SECS.
HIGH TEMPERATURE REFLOW COMPATIBLE - 230°C/90 SEC MAX.

ORIGINATED BY	DATE	TITLE MagJack® 10/100/1000BT TAB UP SHIELDED PATENTED	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REFERENCE		bel COMPONENTS FOR A CONNECTED PLANET
RS Zhang	04-22-10		SI-51014-F	TOL. IN INCH		UNIT : INCH [mm]	REV. : A1	
DRAWN BY	DATE		FILE NAME	.X		SCALE : N/A	SIZE : A4	
RS Zhang	04-22-10		SI-51014-F.DWG	.XX			PAGE : 3	
				.XXX	±0.005			





1. THE SUGGESTED PANEL OPENING IS INTENDED TO GIVE THE USER THE ABILITY TO HAVE REASONABLE JACK / PANEL CLEARANCES YET MAINTAIN RELIABLE GROUNDING CAPABILITY.
2. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ± 0.005 [0.13]

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.	[] METRIC DIM. AS REFERENCE		
RS Zhang	04-22-10	MagJack® 10/100/1000BT TAB UP SHIELDED PATENTED	SI-51014-F	TOL. IN INCH	UNIT : INCH [mm]	REV. :	A1
DRAWN BY	DATE		FILE NAME	.X	SCALE : N/A	SIZE :	A4
RS Zhang	04-22-10		SI-51014-F.DWG	.XX		PAGE :	4
				.XXX	± 0.005		