

DATA SHEET

SURGE CHIP RESISTORS

SR series

20%, 10%, 5%

sizes 0805/1206/1218/2010/2512

RoHS compliant & Halogen free



Product specification – Mar 18, 2011 V.1



SCOPE

This specification describes SR0805 to SR2512 chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

- Telecommunications
- Power supplies

FEATURES

- Superior to SR series in pulse withstanding voltage and surge withstanding voltage.
- MSL class: MSL I
- Halogen free epoxy
- RoHS compliant
 - Products with lead-free terminations meet RoHS requirements
 - Pb-glass contained in electrodes, resistor element and glass are exempted by RoHS
- Reduce environmentally hazardous waste
- High component and equipment reliability

ORDERING INFORMATION - GLOBAL PART NUMBER

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

SR XXXX X X X XX XXXX L

(1) (2) (3) (4) (5) (6) (7)

(1) SIZE

0805 / 1206 / 1218 / 2010 / 2512

(2) TOLERANCE

J = $\pm 5\%$

K = $\pm 10\%$

M = $\pm 20\%$

(3) PACKAGING TYPE

R = Paper taping reel

K = Embossed taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Based on spec.

(5) TAPING REEL

07 = 7 inch dia. Reel

10 = 10 inch dia. Reel

13 = 13 inch dia. Reel

(6) RESISTANCE VALUE

1 $\Omega \leq R \leq 100 \text{ K}\Omega$

There are 2~4 digits indicated the resistance value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. 1K2, not 1K20.

Detailed coding rules of resistance are shown in the table of "Resistance rule of global part number".

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (Note)

| Resistance rule of global part number | | Example |
|---------------------------------------|---|---------|
| Resistance coding rule | Example | |
| XRXX (1 to 9.76 Ω) | IR = 1 Ω IR5 = 1.5 Ω 9R76 = 9.76 Ω | |
| XXRX (10 to 97.6 Ω) | 10R = 10 Ω 97R6 = 97.6 Ω | |
| XXXR (100 to 976 Ω) | 100R = 100 Ω | |
| XKXX (1 to 9.76 K Ω) | 1K = 1,000 Ω 9K76 = 9760 Ω | |
| XXKX (10 to 97.6 K Ω) | 10K = 10,000 Ω 97K6 = 976,000 Ω | |
| XXXK (100 K Ω) | 100K = 100,000 Ω | |

ORDERING EXAMPLE

The ordering code for an SR0805 chip resistor, value 10 K Ω with $\pm 5\%$ tolerance, supplied in 7-inch tape reel is: SR0805JR-0710KL.

MARKING

SR1218




Fig. 1 Value=10 KΩ

E-24 series: 3 digits

First two digits for significant figure and 3rd digit for number of zeros

SR0805 / SR1206 / SR2010 / SR2512



Fig. 2 Value=10 KΩ

E-24 series: 3 digits

First two digits for significant figure and 3rd digit for number of zeros

NOTE

For further marking information, please refer to data sheet "Chip resistors marking".

CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive glaze. The resistive glaze is covered by a lead-free glass. The composition of the glaze is adjusted to give the approximately required resistance value. The whole element is covered by a protective overcoat. The top of overcoat is marked with the resistance value. Finally, the two external terminations (Ni/matte tin) are added, as shown in Fig.3.


OUTLINES

Fig. 3 Chip resistor outlines

DIMENSIONS

Table I




| TYPE | L (mm) | W (mm) | H (mm) | l_1 (mm) | l_2 (mm) |
|--------|-----------------|-----------------|-----------------|-----------------|-----------------|
| SR0805 | 2.00 ± 0.10 | 1.25 ± 0.10 | 0.50 ± 0.10 | 0.35 ± 0.20 | 0.35 ± 0.20 |
| SR1206 | 3.10 ± 0.10 | 1.60 ± 0.10 | 0.55 ± 0.10 | 0.45 ± 0.20 | 0.40 ± 0.20 |
| SR1218 | 3.10 ± 0.10 | 4.60 ± 0.10 | 0.55 ± 0.10 | 0.45 ± 0.20 | 0.40 ± 0.20 |
| SR2010 | 5.00 ± 0.10 | 2.50 ± 0.15 | 0.55 ± 0.10 | 0.55 ± 0.15 | 0.50 ± 0.20 |
| SR2512 | 6.35 ± 0.10 | 3.10 ± 0.15 | 0.55 ± 0.10 | 0.60 ± 0.20 | 0.50 ± 0.20 |

For dimension, please refer to Table I

SR0805/1206/2010/2512

SR1218

Side view for all type



YNSC096

Fig. 4 Chip resistor dimensions

ELECTRICAL CHARACTERISTICS

Table 2

| TYPE | POWER | RESISTANCE RANGE | CHARACTERISTICS | | | | |
|--------|-------|--------------------------------------|-----------------------------|----------------------|-----------------------|---------------------------------|---------------------------------------|
| | | | Operating Temperature Range | Max. Working Voltage | Max. Overload Voltage | Dielectric Withstanding Voltage | Temperature Coefficient of Resistance |
| SR0805 | 1/8 W | | | 150 V | 300 V | 300 V | |
| SR1206 | 1/4 W | | | 150 V | 400 V | 500 V | |
| SR1218 | 1 W | E24 5%, 10%, 20% 1 Ω ≤ R ≤ 100 KΩ | -55 °C to +155 °C | 200 V | 400 V | 500 V | ±200 ppm/°C |
| SR2010 | 3/4 W | | | 200 V | 400 V | 500 V | |
| SR2512 | 1 W | | | 200 V | 400 V | 500 V | |

FOOTPRINT AND SOLDERING PROFILES

Recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting".

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

| PACKING STYLE | REEL DIMENSION | SR0805 | SR1206 | SR1218 | SR2010 | SR2512 |
|--------------------------|----------------|--------|--------|--------|--------|--------|
| Paper taping reel (R) | 7" (178 mm) | 5,000 | 5,000 | --- | --- | --- |
| | 10" (254 mm) | 10,000 | 10,000 | --- | --- | --- |
| | 13" (330 mm) | 20,000 | 20,000 | --- | --- | --- |
| Embossed taping reel (K) | 7" (178 mm) | --- | --- | 4,000 | 4,000 | 4,000 |

NOTE

- I. For paper/embossed tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

FUNCTIONAL DESCRIPTION**OPERATING TEMPERATURE RANGE**Range: -55°C to $+155^{\circ}\text{C}$ **POWER RATING**Each type rated power at 70°C :

SR0805 = 1/8 W (0.125W)

SR1206 = 1/4 W (0.25W)

SR1218 = 1 W

SR2010 = 3/4W (0.75W)

SR2512 = 1 W

RATED VOLTAGE



The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(P \times R)}$$

Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

R = Resistance value (Ω)**PULSE LOAD BEHAVIOR**

TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements

| TEST | TEST METHOD | PROCEDURE | REQUIREMENTS |
|--|------------------------|--|---|
| Temperature Coefficient of Resistance (T.C.R.) | MIL-STD-202 Method 304 | At +25/-55 °C and +25/+125 °C Formula: $T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$ Where $t_1 = +25$ °C or specified room temperature $t_2 = -55$ °C or +125 °C test temperature R_1 = resistance at reference temperature in ohms R_2 = resistance at test temperature in ohms | Refer to table 2 |
| Short Time Overload | IEC60115-1 4.13 | 2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature | $\pm(2.0\%+0.05 \Omega)$ |
| High Temperature Exposure | IEC 60068-2-2 | 1,000 hours at $T_A = 155$ °C ± 5 °C, unpowered | $\pm(3.0\%+0.05 \Omega)$ |
| Humidity | IEC 60115-1 4.24.8 | Steady state for 1,000 hours at 40 °C / 95% R.H. RCWV applied for 1.5 hours on and 0.5 hour off | $\pm(3.0\%+0.05 \Omega)$ |
| Life | IEC 60115-1 4.25.1 | 1,000 hours at 70 ± 2 °C, derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required | $\pm(3.0\%+0.05 \Omega)$ |
| Resistance to Soldering Heat | IEC 60068-2-58 | Condition B, no pre-heat of samples Lead-free solder, 260 ± 5 °C, 10 ± 1 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol | $\pm(1.0\%+0.05 \Omega)$ No visible damage |
| Temperature Cycling | JESD22-A104C | -55/+125 °C for 1 cycle per hour, with 5 cycles. Devices mounted | $\pm(1.0\%+0.05 \Omega)$ |

| TEST | TEST METHOD | PROCEDURE | REQUIREMENTS |
|----------------------------|------------------------------------|--|---|
| Solderability - Wetting | J-STD-002 | Electrical Test not required Magnification 50X SMD conditions: Immerse the specimen into the solder pot at $235 \pm 3^\circ\text{C}$ for 2 ± 0.5 seconds. | Well tinned ($\geq 95\%$ covered) No visible damage |
| Board Flex | IEC 60068-2-21 IEC 60115-1 4.33 | Chips mounted on a 90mm glass epoxy resin PCB (FR4) Bending for 0805: 3 mm 1206 and above: 2 mm Holding time: minimum 60 seconds | $\pm (1.0\% + 0.05 \Omega)$ |

REVISION HISTORY

| REVISION | DATE | CHANGE NOTIFICATION | DESCRIPTION |
|-----------|--------------|---------------------|--|
| Version 1 | Mar 18, 2011 | - | <ul style="list-style-type: none">- Change to dual brand datasheet that describes SR0805 to SR2512 with RoHS compliant- Define global part number |
| Version 0 | Oct 19, 2004 | - | - |

"Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products are unchanged. Any product change will be announced by PCN."

"The reimbursement is limited to the value of the products."

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yageo](#):

[SR1206JR-072R2L](#) [SR1206JR-07150RL](#) [SR1206JR-0710RL](#) [SR1206JR-0710KL](#) [SR1206JR-0736RL](#) [SR1206JR-073R3L](#) [SR1206JR-074R7L](#) [SR1206JR-076R8L](#) [SR1206JR-0768RL](#) [SR1206JR-0747RL](#) [SR1206JR-0733RL](#) [SR0805JR-0710KL](#) [SR1206JR-07100RL](#) [SR1206JR-0712RL](#) [SR1206JR-0715RL](#) [SR1206JR-071KL](#) [SR1206JR-0722RL](#) [SR1206JR-0727RL](#) [SR1206JR-072KL](#) [SR1206JR-073R9L](#) [SR1206JR-0751KL](#) [SR1206JR-0756RL](#) [SR1206JR-075K1L](#) [SR1206JR-0782RL](#) [SR1218KK-071RL](#) [SR1218KK-073R3L](#) [SR2512KK-0722RL](#) [SR2512MK-071R1L](#) [SR0603KR-7W1RL](#) [SR1206JR-072K2L](#) [SR1206JR-07470RL](#) [SR1206JR-07390RL](#) [SR1206JR-073K3L](#) [SR1206JR-072R7L](#) [SR0805JR-0710RL](#) [SR0805JR-071RL](#) [SR1206JR-0715KL](#) [SR1206JR-075R1L](#) [SR1206JR-071RL](#) [SR1206JR-07200RL](#) [SR1206JR-076K8L](#) [SR1206JR-0751RL](#) [SR0805JR-0730RL](#) [SR0805JR-071KL](#) [SR1206JR-071R2L](#) [SR0805JR-07820RL](#) [SR1206JR-7W30RL](#) [SR1206JR-074K7L](#) [SR1206JR-0730RL](#) [SR1206JR-0720RL](#) [SR1206JR-0775RL](#) [SR0603JR-7W1RL](#) [SR1206JR-071R5L](#) [SR2512JK-07150RL](#) [SR2512JK-072RL](#) [SR1206JR-0730KL](#) [SR2512JK-07160RL](#) [SR0402JR-7W1RL](#) [SR1206JR-0739RL](#) [SR1206JR-0712KL](#)