

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [112095-5010](#)
Status: **Active**
Overview: [Brad® Harsh-Duty IO Modules](#)
Description: Brad® HarshIO Digital Module for Ethernet/IP, Classic 60mm, IP67, 8 Ports M12, 8 Inputs / 8 Outputs, PNP, 5 pole Power



Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial I/O Modules
Series [112095](#)
Application Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals ODVA, UL, cUL, CE
Current - Maximum Output 2A per Channel
Format Classic (60mm)
I/O Ports 8x M12
IP Rating IP67
Mechanical Shock 10G, 11ms, 3 AXIS
Overview [Brad® Harsh-Duty IO Modules](#)
Product Literature Order No 987650-5285
Product Name HarshIO EtherNet/IP
Protocol EtherNet/IP
Software Downloads [/molex/mysst/searchBrad.action?itemSoftware=true&itemDocument=true&itemTechNote=true&itemDemo=true&RPP=10&legacy=false&partnumber=DxU883906226602](#)

UPC 883906226602

Physical

Bus Input 4-pole Micro-Change® (M12), D-Coded, Female
Bus Output 4-pole Micro-Change® (M12), D-Coded, Female
Housing Width 60.00mm
I/O Connector 5-pole Micro-Change® (M12), A-Coded, Female
I/O Signal Mix 8 input / 8 output
Net Weight 640.000/g
Power Input 5-pole Mini-Change®, Male
Power Output 5-pole Mini-Change®, Female
Temperature Range - Operating -25°C to +70°C
Vibration IEC 60068-2-6

Electrical

EMC IEC 61000-6-2
Input Delay 2.5ms
Input Device Supply 200 mA per port at 25°C
Input Type PNP or Dry Contact

Material Info

Old Part Number TCDEI-888P-D1U

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[112095Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION