




REVISIONS					
29NOV01 RH					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECO-16-004800	08SEP2016	NK	MZ




1	CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
2	.000030 MIN GOLD FOR A LENGTH OF .250 MIN FROM MATING END OVER .000050 MIN NICKEL.
3	.000100 MIN TIN-LEAD OVER .000050 MIN NICKEL ON THIS END.
4	.000100 MIN TIN OVER .000050 MIN NICKEL ON THIS END.

OBSOLETE		.618	213798-3
		.244	213798-2
		.618	213798-1
	POST FINISH	DIM L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06-30-94		 TE Connectivity			
		D.BROCKWAY 07-06-94					
		R.STONE					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE ASSEMBLY, 23-24, STANDARD SEX, POSTED CONTACTS, CPC			
		APVD —				NAME	
		PRODUCT SPEC					
		108-10024					
		APPLICATION SPEC					
		—		SIZE			
MATERIAL		FINISH		CAGE CODE			
PIN: BRASS		—		DRAWING NO			
RECEPTACLE: NYLON, BLACK				RESTRICTED TO			
		WEIGHT		—			
		CUSTOMER DRAWING		A2			
				00779			
				C-213798			
				SCALE 2:1			
				SHEET 1 of 2			
				REV D1			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BROCKWAY 06-30-94	TE Connectivity			
		CHK R.STONE 07-06-94				
DIMENSIONS: INCHES		APVD -	NAME			
		PRODUCT SPEC 108-10024	RECEPTACLE ASSEMBLY, 23-24,STANDARD SEX, POSTED CONTACTS, CPC			
		APPLICATION SPEC -				
MATERIAL PIN: BRASS RECEPTACLE: NYLON, BLACK		FINISH -	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=213798
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 of 2	REV D1	