





- 1
- MATERIAL: HOUSING-PCT POLYESTER, BLACK, IR COMPATIBLE, UL 94V-0.
TERMINALS-.013 [0.33] THICK PHOS BRONZE PLATED WITH .000050 [1.27μm] THICK HARD GOLD IN LOCALIZED AREA AND .000150 [3.81μm] THICK TIN-LEAD IN SOLDER AREA OVER .000050 [1.27μm] THICK NICKEL UNDERPLATE.
SHIELD-.010 [0.254] THICK COPPER ALLOY PLATED WITH .000080 [2.03μm] MINIMUM TIN-LEAD OVER .000100 [2.54μm] MINIMUM COPPER.
- 2
- JACK CAVITY COMFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3.
- ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 4
- THIS HOLE IS REQUIRED FOR 557572-1 AND 557572-3.



VIEW APPLIES TO 557572-3 ONLY

SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION

3	PANEL GROUND SHIELD	557572-3
2	2 GROUND TABS	557572-2
3	3 GROUND TABS	557572-1
NO. OF HOLES	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.25 [.011]
3 PLC	±0.13 [.0051]
4 PLC	±
ANGLES	±
FINISH	±

DWN
V. SLACK
12MAR92

CHK
B. FOX
10JUN92

APVD
G. REED
15JUN92

PRODUCT SPEC
108-1392

APPLICATION SPEC
114-2048

WEIGHT
-

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
MODULAR JACK ASSEMBLY,
6 PORT,8 POSITION,
RIGHT ANGLE, SHIELDED

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-557572

SCALE
2:1

SHEET
1 OF 1

REV
B