



PRODUCT SPECIFICATION

POWER EDGE CONNECTOR SYSTEM

1.0 SCOPE

This Product Specification covers the printed circuit board (PCB) and bus bar Power Edge Connector System mated with Edge Card PCB or Bus bar.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBER(S)

Power only and Mixed Power-Signal connector series:

45719 – Power Edge Connector, Power Only, Solder,

45714 – Power Edge Connector, Power Only, Press-Fit,

45844 – Power Edge Connector, Mixed Power/Signal, Solder,

45845 – Power Edge Connector, Mixed Power/Signal, Press-Fit.

2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

Housing Material: Liquid Crystal Polymer (LCP), 94V-0, Color: Black

Terminal Material: Copper Alloys (see individual drawings for details)

Plating: See individual drawings for details.

2.3 SAFETY AGENCY APPROVALS

UL File Number: E29179

CSA File Number: 1482777 (LR 19980)

TUV File Number: R 72042763

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

3.1 See sales drawings and the other sections of this specification for the necessary referenced documents and specifications.

3.2 Test Summary: TS-45719-001

4.0 RATINGS

4.1 VOLTAGE

Power Contact: 250 Volts.

4.2 CURRENT

Power Contact: 40A, per mated contact.

Power Contact Current Interruption: 40A at 50V per mated contact (when mated with customer-supplied metal blade or bus bar).

Signal Contact: 3A, per mated contact.

4.3 TEMPERATURE

Operating: - 40°C to + 105°C (including 30°C temperature rise for current rating)

Nonoperating: - 40°C to + 105°C

<u>REVISION:</u> B	Added CSA, TUV, chart. UCP2005-0918 2004 / 12 / 03 Margulis	<u>TITLE:</u> PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM	<u>SHEET No.</u> 1 of 6
<u>DOCUMENT NUMBER:</u> PS-45719-001	<u>CREATED / REVISED BY:</u> MARGULIS	<u>CHECKED BY:</u> MARGULIS	<u>APPROVED BY:</u> MARGULIS



PRODUCT SPECIFICATION

POWER EDGE CONNECTOR SYSTEM

5.0 PERFORMANCE

5.1 ELECTRICAL REQUIREMENTS

DESCRIPTION	TYPE	TEST CONDITION	REQUIREMENT
Contact Resistance (Low Level) (EIA-364-23)	Power	Mate connectors with PCB, apply maximum voltage of 20mV and a current of 100 mA	1 milliohms MAX.
	Signal		15 milliohms MAX.
Contact Resistance @ Rated Current	Power	Mate connectors with PCB, apply a maximum voltage of 20mV at the rated current.	1 milliohms MAX. (initial)
	Signal		15 milliohms Max (initial)
Insulation Resistance (EIA-364-21)	Power	Apply 500 VDC between adjacent terminals or ground.	5,000 Megohms Minimum
	Signal		
Dielectric Strength (EIA-364-20)	Power	Apply 1500 VDC for 1 minute between adjacent terminals or ground.	No Breakdown
	Signal		

5.2 MECHANICAL REQUIREMENTS

DESCRIPTION	TYPE	TEST CONDITION	REQUIREMENT
Mating Force, Single Segment (EIA-364-37)	Power	Mate connectors with PCB at a rate of 25+/-6mm per minute	8.8 N TYP. 2.0 lbf TYP.
	Signal		1.4 N TYP. 5.0 ozf TYP.
UnMating Force, Single Segment (EIA-364-37)	Power	Unmate connectors and PCB at a rate of 25+/-6mm per minute	4.4 N TYP. 1.0 lbf TYP.
	Signal		0.14 N TYP. 0.5 ozf TYP.
Durability w/o Environment (EIA-364-09)	Power	Mate connectors with PCB 250 cycles at a maximum rate of 10 cycles per minute.	1 milliohms Max. change
	Signal		15 milliohms Max. change
Contact Retention (EIA-364-29)	Power	Axial pullout force on the terminal in the housing at a rate of 25+/-6mm per minute.	22 N TYP. 5.0 lbf TYP.
	Signal		22 N TYP. 5.0 lbf TYP.

REVISION:	Added CSA, TUV, chart.	TITLE:	PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM	SHEET No.
B	UCP2005-0918 2004 / 12 / 03 Margulis			2 of 6
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-45719-001		MARGULIS	MARGULIS	MARGULIS



PRODUCT SPECIFICATION

POWER EDGE CONNECTOR SYSTEM

5.3 ENVIRONMENTAL REQUIREMENTS

DESCRIPTION	TYPE	TEST CONDITION	REQUIREMENT
Vibration (EIA 364-28)	Power	Mate connectors with PCB and vibrate per EIA 364-28, test condition VII, letter "D", 15 minutes each axis.	1 milliohms Max change. Discontinuity < 1 microsec
	Signal		10 milliohms Max change. Discontinuity < 1 microsec
Shock (EIA-364-27)	Power	Mate connectors with PCB and shock at 50 g with ½ sine wave (11 milliseconds) shocks in the X, Y, Z axes (18 shocks total)	1 milliohms Max change. Discontinuity < 1 microsec
	Signal		10 milliohms Max change. Discontinuity < 1 microsec
Humidity (EIA-364-31)	Power	Mate connectors with PCB: expose to 40+/-2 deg. C with relative humidity of 90-95% for 96 hours.	1 milliohms Max change.
	Signal		10 milliohms Max change.
Solderability (EIA-364-52)	Power	Dip connector terminal tails in solder, duration 5 sec. Solder temperature 245 +/- 5 deg. C.	Solder coverage: 95% Minimum
	Signal		
Thermal Shock (EIA-364-TP-32)	Power	Mate connectors with PCB, expose to 5 cycles from -55 deg. C to 85 deg. C per EIA-364-TP-32	1 milliohms Max change.
	Signal		10 milliohms Max change.
Temperature Life (EIA-364-17)	Power	Mate connectors with PCB, expose to 240 hours at 105 deg. C Per EIA-364-17 Method A	1 milliohms Max change
	Signal		10 milliohms Max change.

6.0 COMPLIANT PIN INTERFACE PERFORMANCE

6.1 Insertion and Withdrawal Force (3 times in the same hole) per EIA-364-37

COMPONENT	TEST CONDITION	REQUIREMENT	
		INSERT.	WITHDR.
Power Contact (Single section)	Insert the single compliant section into the PTH, extract the section from the hole after 12 hrs, repeat 2 times (new part in the same hole)	98 N 22 lb MAX.	45 N 10.1 lb. MIN.
Signal Contact (Single contact)	Insert the single compliant pin contact into the PTH, extract the contact from the hole after 12 hrs, repeat 2 times (new part in the same hole)	98 N 22 lb MAX.	45 N 10.1 lb. MIN.


REVISION:	Added CSA, TUV, chart. UCP2005-0918 2004 / 12 / 03 Margulis	TITLE:	PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM		SHEET No.
B					3 of 6
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-45719-001		MARGULIS	MARGULIS	MARGULIS	



PRODUCT SPECIFICATION

POWER EDGE CONNECTOR SYSTEM

7.0 RECOMMENDED TIN PLATED THROUGH HOLE DIMENSIONS:



Recommended PCB thickness .093 min.

Recommended Plated Through Hole dimensions:

Drilled Hole Dia.: 1.15/.0453 +/- 0.013/.0005

Copper Plate Thickness: 0.03/.001 Min. (per surface)

Tin Plate Thickness: 0.008/.0003 Min. (per surface)

Finished Hole Dia.: 1.02/.040 +/- 0.08/.003

8.0 PACKAGING:

Parts shall be packaged to protect against damage during handling, transit and storage.

REVISION: B	Added CSA, TUV, chart. UCP2005-0918 2004 / 12 / 03 Margulis	TITLE: PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM	SHEET No. 4 of 6
DOCUMENT NUMBER: PS-45719-001	CREATED / REVISED BY: MARGULIS	CHECKED BY: MARGULIS	APPROVED BY: MARGULIS




PRODUCT SPECIFICATION


POWER EDGE CONNECTOR SYSTEM

10. TEST SEQUENCES:

10.1 Reliability Test Sequences (per EIA-364-1000 Test Groups 1,2,and 3):



10.2 Electrical Performance Test Sequence:



10.3 Miscellaneous Testing

- Insulation Resistance
- Dielectric Strength
- Mating/Unmating Force
- Contact Retention
- Solderability
- Compliant Pin Insertion/Withdrawal Force
- Contact Normal Force

REVISION: B	Added CSA, TUV, chart. UCP2005-0918 2004 / 12 / 03 Margulis	TITLE: PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM	SHEET No. 5 of 6
DOCUMENT NUMBER: PS-45719-001	CREATED / REVISED BY: MARGULIS	CHECKED BY: MARGULIS	APPROVED BY: MARGULIS




PRODUCT SPECIFICATION

POWER EDGE CONNECTOR SYSTEM

11. CURRENT CARRYING CAPACITY:

Power Edge, Dual Sided - 5oz. Cu PCB
T-Rise Current Chart



REVISION: B	Added CSA, TUV, chart. UCP2005-0918 2004 / 12 / 03 Margulis	TITLE: PRODUCT SPECIFICATION FOR POWER EDGE CONNECTOR SYSTEM	SHEET No. 6 of 6
DOCUMENT NUMBER: PS-45719-001	CREATED / REVISED BY: MARGULIS	CHECKED BY: MARGULIS	APPROVED BY: MARGULIS