



PART NUMBER	8609			78				8	
PIN OUT									
rows a-b-c	_____	-	_____	3	-	_____	48		
rows a-c	_____	-	_____	4	-	_____	32		
NUMBER OF CONTACTS									
TERMINATION									
L = 2.70 ±0.25 (.106)	_____	-	_____	-	_____	-	24		
L = 4.65 ±0.25 (.183)	_____	-	_____	-	_____	-	14		
OPTIONS									
no option	_____	-	_____	-	_____	-	7		
with harpoons	_____	-	for PCB thickness 1.6 mm	_____	_____	-	H		
	_____	-	for PCB thickness 2.4 mm	_____	_____	-	A		
	_____	-	for PCB thickness 3.2 mm	_____	_____	-	R		
PERFORMANCE CLASS									
DIN 41612 class 3	_____	-	_____	-	_____	-	4		
DIN 41612 class 2	_____	-	_____	-	_____	-	5		
DIN 41612 class 1	_____	-	_____	-	_____	-	6		
TERMINATION TYPE									
TIN LEAD	_____	-	_____	-	_____	-	_____	-	000E1
LEAD FREE	_____	-	_____	-	_____	-	_____	-	E1LF

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	ROUILLARD	1997/10/27	ANGULAR	LINEAR	0.X		±0.1		size A3	Scale 1.5		
Eng	TARON	1997/10/27			0.XX		±0.1					
Chr	LEGARE	1997/10/27			0.XXX		±0.1					
Appr	LEGARE	1997/10/27	0.XX' ±2'						ECN L506-0095			
			Product family				DIN 8609		Spec ref -			
			title STRAIGHT MALE - STYLE R SOLDER TO BOARD				dwg no C-8609-0641				Rev. C	
catalog no			-				CUSTOMER		sheet 1 of 1			

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

rev	ech no	dr	date
A	-	-	1997/10/2
B	LS05-001	JTA	2005/03/0
C	LS06-0095	LGO	2006/06/2
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-