

SERIES

PTHFxxxxR
PTKMxxxxR
PTHF
PTKM

RoHS
Compliant

Traditional
First Quality

Toroidal Power Chokes



Actual Size

Horizontal or Vertical Mounting

Excellent electromagnetic shielding

Applications Use Series PTHF for high DC saturation applications; use Series PTKM for low AC core loss applications.

DC Resistance at 25°C

Rated Idc based upon 40°C maximum rise from 90°C ambient with 0 Arms

Self Leads

Solder coated along entire length

Mounting Toroids can be provided in a vertical or horizontal mount style. Suffix Part Number with "H" for horizontal mount.

dl Incremental Current is the value indicated in the table that will cause an approximate percentage drop in inductance

Marking

DELEVAN and part number.


Example: PTHF50R-121

DELEVAN PTHF50R-121


Physical Parameters on Next Page

*Complete part # must include series # PLUS the dash #

NUMBER*	PART	INDUCTANCE (μH) @ 1 kHz ±10%	RATED IDC (AMPS)	ΔL 10%	dl ADC @ 10%	ΔL 20%	dl ADC @ 20%	DC RESISTANCE MAXIMUM (OHMS)	SRF MINIMUM (MHz)	Power Inductors
SERIES PTHF HIGH SATURATION CORE										
PTHF10-50	10	7.36	6.0	8.7	0.010	35.0				
PTHF25-50	25	5.20	3.6	5.3	0.020	10.0				
PTHF50-50	50	3.93	2.0	3.1	0.035	7.0				
PTHF75-50	75	3.47	1.6	2.5	0.045	5.0				
PTHF100-50	100	3.14	1.5	2.2	0.055	4.0				
PTHF150-50	150	2.33	1.2	1.8	0.100	2.0				
PTHF200-50	200	1.97	1.0	1.6	0.140	1.7				
PTHF250-50	250	1.84	0.9	1.4	0.160	1.5				
PTHF330-50	330	1.69	0.8	1.2	0.190	1.0				
PTHF10-121	10	8.27	9.0	14.0	0.010	20.0				
PTHF25-121	25	6.34	7.0	10.5	0.017	8.0				
PTHF50-121	50	4.77	3.9	6.0	0.030	4.0				
PTHF75-121	75	3.90	3.9	5.8	0.045	3.0				
PTHF100-121	100	3.24	3.4	4.7	0.065	2.0				
PTHF150-121	150	2.68	3.3	4.8	0.095	1.5				
PTHF250-121	250	2.07	2.2	3.2	0.160	1.0				
PTHF10-59	10	14.50	15.0	20.0	0.008	20.0				
PTHF25-59	25	9.80	11.0	16.0	0.011	8.0				
PTHF50-59	50	6.90	8.3	12.0	0.022	4.0				
PTHF75-59	75	5.90	6.7	9.1	0.030	3.0				
PTHF100-59	100	4.90	6.5	8.2	0.044	2.0				
PTHF150-59	150	4.50	4.2	6.0	0.052	1.0				
PTHF250-59	250	3.50	4.0	5.6	0.088	1.0				
PTHF500-59	500	2.60	2.7	3.8	0.160	0.8				
PTHF750-59	750	2.10	1.8	2.7	0.240	0.6				
PTHF25-894	25	12.80	13.5	20.0	0.008	8.0				
PTHF50-894	50	9.90	10.8	15.2	0.016	4.0				
PTHF75-894	75	8.00	8.0	12.0	0.023	3.0				
PTHF100-894	100	8.00	7.1	10.6	0.023	2.0				
PTHF150-894	150	6.50	6.0	9.0	0.035	1.0				
PTHF250-894	250	5.00	4.6	6.8	0.060	1.0				
PTHF500-894	500	3.40	3.1	4.6	0.131	0.8				
PTHF750-894	750	3.00	2.7	4.0	0.160	0.6				
PTHF1000-894	1000	2.40	2.3	3.5	0.235	0.4				
SERIES PTKM FERROUS ALLOY CORE										
PTKM10-50	10	7.36	1.70	3.30	0.010	35.0				
PTKM25-50	25	5.20	1.00	1.90	0.020	10.0				
PTKM50-50	50	3.93	0.70	1.30	0.035	7.0				
PTKM75-50	75	3.47	0.60	1.10	0.045	5.0				
PTKM100-50	100	3.14	0.50	0.96	0.055	4.0				
PTKM150-50	150	2.33	0.40	0.78	0.100	2.0				
PTKM200-50	200	1.97	0.35	0.65	0.140	1.7				
PTKM250-50	250	1.84	0.31	0.59	0.160	1.5				
PTKM330-50	330	1.69	0.27	0.50	0.190	1.0				
PTKM10-121	10	8.27	5.30	9.10	0.010	20.0				
PTKM25-121	25	6.34	3.30	5.70	0.017	8.0				
PTKM50-121	50	4.77	2.30	4.00	0.030	4.0				
PTKM75-121	75	3.90	1.80	3.10	0.045	3.0				
PTKM100-121	100	3.24	1.60	2.80	0.065	2.0				
PTKM150-121	150	2.68	1.30	2.20	0.095	1.5				
PTKM250-121	250	2.07	0.90	1.70	0.160	1.0				
PTKM10-59	10	14.50	7.60	13.00	0.008	20.0				
PTKM25-59	25	9.80	4.70	8.30	0.011	8.0				
PTKM50-59	50	6.90	3.30	5.70	0.022	4.0				
PTKM75-59	75	5.90	3.00	4.90	0.030	3.0				
PTKM100-59	100	4.90	2.40	4.20	0.044	2.0				
PTKM150-59	150	4.50	1.90	3.40	0.052	1.0				
PTKM250-59	250	3.50	1.50	2.70	0.088	1.0				
PTKM500-59	500	2.60	1.10	1.80	0.160	0.8				
PTKM750-59	750	2.10	0.90	1.60	0.240	0.6				
PTKM25-894	25	12.80	6.60	11.00	0.008	8.0				
PTKM50-894	50	9.90	4.20	7.40	0.016	4.0				
PTKM75-894	75	8.00	3.70	6.40	0.023	3.0				
PTKM100-894	100	8.00	3.50	6.00	0.023	2.0				
PTKM150-894	150	6.50	2.30	4.30	0.035	1.0				
PTKM250-894	250	5.00	1.90	3.20	0.060	1.0				
PTKM500-894	500	3.40	1.40	2.50	0.131	0.8				
PTKM750-894	750	3.00	1.20	2.10	0.160	0.6				
PTKM1000-894	1000	2.40	1.00	1.80	0.235	0.4				

SERIES**PTHFxxxxR & PTKMxxxxR**
PTHF & PTKMRoHS
CompliantTraditional
First Quality**Toroidal Power Chokes – Horizontal or Vertical Mount**

Vertical Configuration



Horizontal Configuration

PHYSICAL PARAMETERS* **Nominal Dimensions** Allow up to 10% of nominal for maximum size** **Part Number** Insert HF of KM for complete part number, and suffix "H" for horizontal mounting*Electrical Information on Preceding Page*

PART NUMBER	A Nominal*		B Nominal*		C Typical		D Nominal*		E Nominal*		F Nominal*	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm
PT**10-50	0.625	15.88	0.300	7.62	0.250	6.35	0.500	12.70	0.036	0.91	0.600	15.24
PT**25-50	0.625	15.88	0.300	7.62	0.250	6.35	0.500	12.70	0.032	0.81	0.600	15.24
PT**50-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.028	0.71	0.600	15.24
PT**75-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.025	0.63	0.600	15.24
PT**100-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.025	0.63	0.600	15.24
PT**150-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.020	0.51	0.600	15.24
PT**200-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.018	0.46	0.600	15.24
PT**250-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.018	0.46	0.600	15.24
PT**330-50	0.625	15.87	0.300	7.62	0.250	6.35	0.500	12.70	0.018	0.46	0.600	15.24
PT**10-121	0.820	20.83	0.400	10.16	0.320	8.13	0.500	12.70	0.040	1.02	0.780	19.81
PT**25-121	0.820	20.83	0.400	10.16	0.320	8.13	0.500	12.70	0.040	1.02	0.780	19.81
PT**50-121	0.820	20.83	0.400	10.16	0.320	8.13	0.500	12.70	0.036	0.91	0.780	19.81
PT**75-121	0.820	20.83	0.400	10.16	0.320	8.13	0.500	12.70	0.032	0.81	0.780	19.81
PT**100-121	0.820	20.83	0.400	10.16	0.320	8.13	0.500	12.70	0.028	0.71	0.780	19.81
PT**150-121	0.850	21.59	0.400	10.16	0.320	8.13	0.500	12.70	0.025	0.63	0.780	19.81
PT**250-121	0.850	21.59	0.400	10.16	0.320	8.13	0.500	12.70	0.023	0.58	0.780	19.81
PT**10-59	1.100	27.94	0.475	12.06	0.370	9.40	0.500	12.70	0.051	1.30	1.050	26.67
PT**25-59	1.100	27.94	0.475	12.06	0.370	9.40	0.500	12.70	0.051	1.30	1.050	26.67
PT**50-59	1.100	27.94	0.475	12.06	0.370	9.40	0.500	12.70	0.045	1.14	1.050	26.67
PT**75-59	1.100	27.94	0.475	12.06	0.370	9.40	0.500	12.70	0.040	1.02	1.050	26.67
PT**100-59	1.100	27.94	0.475	12.06	0.370	9.40	0.500	12.70	0.036	0.91	1.050	26.67
PT**150-59	1.100	27.94	0.475	12.06	0.450	11.43	0.500	12.70	0.036	0.91	1.050	26.67
PT**250-59	1.150	29.21	0.475	12.06	0.450	11.43	0.500	12.70	0.032	0.81	1.050	26.67
PT**500-59	1.150	29.21	0.475	12.06	0.450	11.43	0.500	12.70	0.028	0.71	1.050	26.67
PT**750-59	1.150	29.21	0.475	12.06	0.450	11.43	0.500	12.70	0.025	0.63	1.050	26.67
PT**25-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.064	1.3	1.250	31.75
PT**50-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.051	1.30	1.250	31.75
PT**75-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.051	1.30	1.250	31.75
PT**100-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.051	1.30	1.250	31.75
PT**150-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.045	1.14	1.250	31.75
PT**250-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.040	1.02	1.250	31.75
PT**500-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.032	0.81	1.250	31.75
PT**750-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.032	0.81	1.250	31.75
PT**1000-894	1.300	33.02	0.650	16.51	0.600	15.24	0.750	19.05	0.028	0.71	1.250	31.75

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[PTHF100-59H](#) [PTHF10-59H](#) [PTHF25-59H](#) [PTHF25-894H](#) [PTHF10-50](#) [PTHF25-50](#) [PTHF50-50](#) [PTHF75-50](#)
[PTHF100-50](#) [PTHF150-50](#) [PTHF200-50](#) [PTHF250-50](#) [PTHF330-50](#) [PTHF10-121](#) [PTHF25-121](#) [PTHF50-121](#)
[PTHF75-121](#) [PTHF100-121](#) [PTHF150-121](#) [PTHF250-121](#) [PTHF10-59](#) [PTHF25-59](#) [PTHF50-59](#) [PTHF75-59](#)
[PTHF100-59](#) [PTHF150-59](#) [PTHF250-59](#) [PTHF500-59](#) [PTHF750-59](#) [PTHF25-894](#) [PTHF50-894](#) [PTHF75-894](#)
[PTHF100-894](#) [PTHF150-894](#) [PTHF250-894](#) [PTHF500-894](#) [PTHF750-894](#) [PTHF1000-894](#) [PTHF10-50H](#) [PTHF25-](#)
[50H](#) [PTHF50-50H](#) [PTHF75-50H](#) [PTHF100-50H](#) [PTHF150-50H](#) [PTHF200-50H](#) [PTHF250-50H](#) [PTHF330-50H](#)
[PTHF10-121H](#) [PTHF25-121H](#) [PTHF50-121H](#) [PTHF75-121H](#) [PTHF100-121H](#) [PTHF150-121H](#) [PTHF250-121H](#)
[PTHF50-59H](#) [PTHF75-59H](#) [PTHF150-59H](#) [PTHF250-59H](#) [PTHF500-59H](#) [PTHF750-59H](#) [PTHF50-894H](#) [PTHF75-](#)
[894H](#) [PTHF100-894H](#) [PTHF150-894H](#) [PTHF250-894H](#) [PTHF500-894H](#) [PTHF750-894H](#) [PTHF1000-894H](#)
[PTHF10R-50](#) [PTHF25R-50](#) [PTHF50R-50](#) [PTHF75R-50](#) [PTHF100R-50](#) [PTHF150R-50](#) [PTHF200R-50](#) [PTHF250R-](#)
[50](#) [PTHF330R-50](#) [PTHF10R-121](#) [PTHF25R-121](#) [PTHF50R-121](#) [PTHF75R-121](#) [PTHF100R-121](#) [PTHF150R-121](#)
[PTHF250R-121](#) [PTHF10R-59](#) [PTHF25R-59](#) [PTHF50R-59](#) [PTHF75R-59](#) [PTHF100R-59](#) [PTHF150R-59](#) [PTHF250R-](#)
[59](#) [PTHF500R-59](#) [PTHF750R-59](#) [PTHF25R-894](#) [PTHF50R-894](#) [PTHF75R-894](#) [PTHF100R-894](#) [PTHF150R-894](#)
[PTHF250R-894](#) [PTHF500R-894](#)