


**Part Number: 501876-1630**

2.00mm Pitch iGrid™ Wire-to-Board Header, Dual Row, Right Angle, with Kinked PC Tails, 16 Circuits



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	501876
Category:	PCB Headers
Overview:	iGrid™

Mates With Part(s):[501646 Housing](#)**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:** Not Reviewed**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	PCB Headers
Series	501876
Application	Signal, Wire-to-Board
Overview	iGrid™
Product Name	iGrid™

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm, 1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-25°C to +85°C

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	2A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

UPC	822350303095
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-501646-001, RPS-501646-006, RPS-501646-007
Sales Drawing	SD-501876-002

Application Tooling

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)