



Products > Audio > XLR > XLR Chassis Connectors > B Series > NC3MBH-E

print

NC3MBH-E

3 pole male XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, steel retention lug, horizontal PCB mount, additional ground contacts

Same as A series with exception of a metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC practice. UL recognized component.



Downloads

- [Product Guide 2012, 02 XLR](#)
- [Drawing NC3MBH-E](#)
- [Drawing NC3MBH-E](#)

Features & Benefits

- Five additional ground contacts
- Smallest XLR receptacles, highest packing density
- Metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC and RF protection
- Housing flammability UL94V-0

Technical Information hide

Product	
Title	NC3MBH-E
Connection Type	XLR
Gender	male
Electrical	
Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 5 mΩ (inner)
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 GΩ (initial)
Rated current per contact	6 A
Rated voltage	50 V
Grounding Options	Separate ground contacts connected to mating connector shell and front panel, no connection to Pin 1
Mechanical	

Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	rear
Chassis shape	B
Mounting	B-Screw

Material	
Contacts	Brass (CuZn35Pb2)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Stahl Ck67
Ring	Zinc diecast (ZnAl4Cu1)
Flange	Black Metal

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Accessories



B-SCREW-1-8



CAS-DUMMY



NDM



SCM

