




DO NOT SCALE
FROM THIS PRINT

UNLESS OTHERWISE NOTED	
DIMENSIONS ARE IN INCHES	TOLERANCES ARE:
ONE DECIMALS ± .1	THREE PLACE DECIMALS ± .005
TWO DECIMALS ± .01	FOUR PLACE DECIMALS ± .0020

S	TITLE:	DUAL ROW 2mm x
		2mm ASSEMBLY

DWG NO: TLE-1XX-XX-X-DV-X
SHEET 1 OF 2



SECT "A-A"

1. MINIMUM PUSHOUT FORCE: .4 lb.
2. COPLANARITY: POS -02 THRU -26: .004
POS -27 THRU -50: .006
3. REPRESENTS A CRITICAL DIMENSION.
4. ALL POSITIONS TO BE PACKAGED IN TUBES.
5. FOR EVERY FINISHED PART, ONE POSITION WILL BE LOST
WHEN CUTTING BODY TO LENGTH.
6. BURR ALLOWANCE: .003 [.08] MAX
7. CUT FLASH TO BE .010 [.25] MAX WITH
NO FLASH ALLOWED IN HOLES OR
EXTENDING BELOW LEADS.
8. END WALLS TO BE .027+/- .005 [.69+/- .13] AFTER CUT.

PATENT NUMBERS
5713755 / 5961339

MATERIAL:
BODY:
VECTRA E130I
COLOR: BLACK
TERMINAL:
PHOSPHER BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: D PURVIS 01-20-97

TLE-1XX-XX-X-DV-X
SHEET 1 OF

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SANTEC INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSMITTED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SANTEC INC.