




1. THIS PART CONFORMS TO REQUIREMENTS FOR DANIELS CRIMP TOOL NO. M300-BT, WITH DANIELS POSITIONER PART NO. SP689, STRIP LENGTH .375, SETTING #1.
2. MATES WITH 212007-1 IN AMPLIMITE CONNECTOR ASSEMBLIES ONLY.
3. FINISH: PLATED GOLD .000050 [0.00127] MIN THK PER MIL-G-45204 OVER NICKEL .000050 [0.00127] MIN THK PER QQ-N-290.
4. FINISH: PLATED GOLD .000030 [0.00076] MIN THK PER MIL-G-45204 OVER NICKEL .000050 [0.00127] MIN THK PER QQ-N-290.
5. WIRE BARREL WILL ACCEPT #12-#14 AWG WIRE.

PRELIMINARY NOT RELEASED FOR PRODUCTION	4	212008-2
	3	212008-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11/10/00	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES [mm]		CHK D.MILLER 11/10/00		
		APVD D.MILLER 11/10/00		NAME ASSEMBLY, SOCKET CONTACT POWER VIII, #12 & #14 AWG
		PRODUCT SPEC 108-10045		
MATERIAL SEE CALLOUTS		APPLICATION SPEC 114-10014		SIZE A2
		FINISH SEE TABLE		
CUSTOMER DRAWING		WEIGHT -	CAGE CODE 00779	DRAWING NO 212008
		SCALE 10:1	SHEET 1 OF 1	REV H