


NEW Product



Patent No. 6,786,736



2 YEAR WARRANTY

All specifications are typical at 12 Vin and 1.5 Vout, full load at 25 °C unless otherwise stated.
 $C_{out} = 100 \mu F$

SPECIFICATIONS

OUTPUT SPECIFICATIONS

Voltage adjustability	0.8-3.63 Vdc	
Setpoint accuracy	±1.3% typ.	
Line regulation	±0.2% typ.	
Load regulation	±1.5% typ.	
Total error band	±3.0% typ.	
Minimum load	0 A	
Overshoot/undershoot	None	
Ripple and noise	5 Hz to 20 MHz	60 mV pk-pk 25 mV rms
Temperature coefficient	±0.01%/ $^{\circ}$ C	
Transient response Slew rate = 0.5 A/ μ s	1.5 Vout	50% to 75% load step 3% max. deviation 10 μ s recovery to within ±1.0%
Remote sense	10% Vo compensation	

EMC CHARACTERISTICS

Electrostatic discharge	EN61000-4-2, IEC801-2
Conducted immunity	EN61000-4-6
Radiated immunity	EN61000-4-3

GENERAL SPECIFICATIONS

Efficiency	@ 12 Vin, 3.3 Vout	91% typ.
Insulation voltage	Non-isolated	
Switching frequency	Fixed	1.3 MHz typ.
Approvals and standards	EN60950-1 UL/cUL60950-1	
Material flammability	UL94V-0	
Dimensions	(LxWxH)	33.02 x 13.46 x 8.10 mm 1.3 x 0.53 x 0.319 inches
Weight	6.3 g (0.22 oz)	
Coplanarity	100 μ m	
MTBF	Telcordia SR-332	3,289,053 hours

INPUT SPECIFICATIONS

Input voltage range	8-14 Vdc	
Input current	No load (max.)	250 mA
Input current (max.)	9.2 A max. @ Io max. and Vout = 3.3 V	
Input reflected ripple	220 mA rms	
Remote ON/OFF	(See Note 1)	
Start-up time	20 ms	

ENVIRONMENTAL SPECIFICATIONS

Thermal performance	Operating ambient, temperature Non-operating	-40 °C to +85 °C -40 °C to +125 °C
MSL	JEDEC J-STD-020C	Level 3

PROTECTION

Short-circuit	Continuous
Thermal	Automatic recovery

International Safety Standard Approvals



UL/cUL CAN/CSA 22.2 No. E174104
UL 60950 File No. E174104



TÜV Product Service (EN60950) Certificate No. B05 06 38572 055
CB report and certificate to IEC60950

OUTPUT POWER (MAX.)	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT (MIN.)	OUTPUT CURRENT (MAX.)	EFFICIENCY (MAX.)	REGULATION	MODEL NUMBER (2, 3)
				LINE	LOAD		
99 W	8-14 Vdc	0.8-3.63 Vdc	0 A	30 A	91%	±0.2%	±1.5% SMT30E-12W3V3J

Part Number System with Options

SMT30E-12W3V3-TJ

Product Family
SMT = Surface Mount

Rated Output Current
30 = 30 Amps

Performance
E = Enhanced Performance

Packaging Options (2)
No '-T' Suffix = Pb-free RoHS 6/6 compliant parts in trays e.g SMT30E-12W3V3J
-TJ = Pb-free RoHS 6/6 compliant part in Tape and Reel e.g SMT30E-12W3V3-TJ

Output Voltage
0.8 Vdc to 3.63 Vdc

Type of Output
W = Wide

Input Voltage
12 = 8 Vdc to 14 Vdc

Output Voltage Adjustment of the SMT30E-12W3V3J Series

The ultra-wide output voltage trim range offers major advantages to users who select the SMT30E-12W3V3J. It is no longer necessary to purchase a variety of modules in order to cover different output voltages. The output voltage can be trimmed in a range of 0.8 Vdc to 3.63 Vdc. When the SMT30E-12W3V3J converter leaves the factory the output has been adjusted to the default voltage of 0.8 V.

Notes

1 The SMT30E features a 'Positive Logic' Remote ON/OFF operation. If not using the Remote ON/OFF pin, leave the pin open (the converter will be on). The Remote ON/OFF pin is referenced to ground.

The following conditions apply for the SMT30E:

Configuration	Converter Operation
Remote pin open circuit	Unit is ON
Remote pin pulled low [Von/off < 0.8 V]	Unit is OFF
Remote pin pulled high [Von/off > 2.8 V]	Unit is ON

A 'Negative Logic' Remote ON/OFF version is also possible with this converter. To order please place the suffix 'R' towards the end of the model number, e.g. SMT30E-12W3V3-TRJ.

2 TSE RoHS 5/6 (non Pb-free) compliant versions may be available on special request, please contact your local sales representative for details.

3 NOTICE: Some models do not support all options. Please contact your local Artesyn representative or use the on-line model number search tool at <http://www.artesyn.com/powergroup/products.htm> to find a suitable alternative.

Notes

A The derating curves represent the condition at which internal components are within the Artesyn derating guidelines.

B Characteristic data has been developed from actual products tested at 25 °C. This data is considered typical data for the converter.

For the most current data and application support visit www.artesyn.com/powergroup/products.htm

NEW Product




Figure 1 - Derating Curve
Vin = 12 V, Output Voltage = 1.0 V (See Note A)




Figure 2 - Derating Curve
Vin = 12 V, Output Voltage = 1.5 V (See Note A)




Figure 3 - Derating Curve
Vin = 12 V, Output Voltage = 1.8 V (See Note A)




Figure 4 - Derating Curve
Vin = 12 V, Output Voltage = 2.5 V (See Note A)




Figure 5 - Efficiency vs Load Current
Vin = 12 V (See Note B)




Figure 6 - Standard Application




Figure 7 - Mechanical Drawing and Pinout Table