

A1

PROJECT NO.
B916823
A98-52300

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE DWN APVD
A1	-	D1	SEE PCN EG00-2505-00-1		20OCT2000 REH VB
		D2	SEE PCN EG00-0134-01-2		11JAN2001 REH VB
		E	SEE PCN EG00-0553-03-2		17FEB2003 LN REH
		E1	SEE PCN EG00-1054-03-1		24MAR2003 LN REH




D

C

B



A

Pro/ENGINEER DRAWING



CODING Z AS DRAWN

D2



NOTES

Bemerkungen

1 AMP-LOGO
AMP-Logo

2 ORDER-NUMBER
Bestell-Nummer

3 REVISIONS-NUMBER
Werkzeugänderungsindex

4 -

5 CAVITY MARKING
Nestmarkierung

6 PACKAGING IN LAYERS ACC. TO AMP-SPEC. 107-18032-300
Lagenverpackung nach AMP-Spez. 107-18032-300

7 MATERIAL MARKING
Werkstoffkennzeichnung

8 PIN TIPS ACC. TO TYCO SPEC. 114-18063
Tabspitzen nach Tyco Spez.

9 ELECTRICAL VALUES ACC. TO 114-18021
elektrische Werte nach

MATING WITH
Passend zu

929051-1 - COVER WITH LEVER
967671-1/-3 - COVER WITH LEVER
968473-1 - MQS SOCKET HSG.

E	1355505-4	A	B	3.6	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 µm)	3
					MODU II PIN	6	CuFe2	TIN PLATED (MIN. THICKN. 1 µm)	2
	1355505-3	A	B	2.8	HOUSING	1	PA6(GB20+GF10)	LIGHTGREY	1
					MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 µm)	3
	1355505-2	A	A	2.8	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 µm)	2
					HOUSING	1	PA6(GB20+GF10)	BLUE	1
A1	1355505-1	D	Z	2.8	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 µm)	3
					MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 µm)	2
D2					HOUSING	1	PA6(GB20+GF10)	BLACK	1
					HOUSING	1	PA6(GB20+GF10)	BLACK	1
C	Assy No.	Rev.Cod.	"L"	Description	Pcs.	Material	Surface Finish	No.	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±0.5
		1 PLC	±0.5
		2 PLC	±0.5
		3 PLC	±
		4 PLC	±
		ANGLES	±°
MATERIAL	-	FINISH	-

DWN	M. Reinhardt	17MA199
CHK	M. Reinhardt	19MAY99
APVD	-	-
PRODUCT SPEC	108-18671-0	
APPLICATION SPEC	114-18314-0	
WEIGHT	-	
CUSTOMER DRAWING		

AMP Deutschland GmbH D - 63225 Langen			
NAME 12POS. MQS PIN HEADER 90°, ASSY 12pol.MQS Stiftleiste 90°, Assy			
SIZE	CAGE CODE	DRAWING NO.	RESTRICTED TO
A2	00779	C-1355505	-
SCALE	5.1	SHEET	OF
		1	REV
			E1