


TOP VIEW
W/WINDSHIELD SHOWN
SCALE 1:1

THE FRONT SOUND PORT IS ADJACENT TO
THE MODEL NUMBER IDENTIFICATION.

FB-BW-30330-000
SHT 1.1




LENGTH	WIRE COLOR		WEIGHT GRAMS
	+ve	-ve	
	RED	BLACK	13.1

DIMENSIONS IN MILLIMETERS [INCHES]

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION	
B	C10107741	7-18-08	Active	B	
A	C10106619	3-6-08			
SCALE: 1:1			DR. BY TT	DATE 3-6-08	
DO NOT SCALE DRAWING			CK. BY GJP	DATE 3-9-08	
TITLE: BOOM MICROPHONE			FB-BW-30330-000		
OUTLINE DRAWING			SHT 1.1	APP. BY GJP	DATE 3-9-08



KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.



NOTES:

1. MICROPHONE TO BE FUNCTIONAL WITH 10 VDC SUPPLY.
2. SENSITIVITY VALUES INDICATED ON THIS SPECIFICATION ARE VALID AT 50% HUMIDITY.
3. SENSITIVITY

FREQUENCY	MIN	NOM	MAX
300	-62.0	-58.0	-54.0
1000	-62.0	-58.0	-54.0
4000	-62.0	-58.0	-54.0
4. TEST CONDITIONS:
HEAD OF BOOM EXPOSED TO 74 dBSPL SWEPT SOUND FIELD AT 6mm FROM VOICE APERTURE.
ARTIFICIAL VOICE: B & K 4227 MOUTH SIMULATOR.
5. FOR MICROPHONE CAPSULE SPEC. SEE NR-25994-D63 SHEET 2.1



LEAD IDENTIFICATION
& TEST CIRCUIT

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
B	C10107741	7-18-08	Active	B
A	C10106619	3-6-08		
WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION			DR. BY	DATE
TITLE: BOOM MICROPHONE FB-BW-30330-000 PERFORMANCE SPECIFICATION SHT 2.1			TT	3-6-08
			CK. BY	DATE
			GJP	3-9-08
			APP. BY	DATE
			GJP	3-9-08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[FB-BW-30330-000](#)