


LOC	DIST	REVISIONS				DAP		
		P	LTR	DESCRIPTION		DATE	DWN	APVD
G	14		G	REV PER ECR 07-017771		21AUG07	JR	MS

D

C

B

A




AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 TIN PLATE 0.00254 [.000100] MIN THK PER MIL-T-10727
- 3 GOLD PLATE PER MIL-G-45204, TYPE II, CLASS I, 0.00127 [.000050] MIN THK.
- 4 COPPER PER ASTM B-152, ANNEALED
- 5 TIN LEAD PLATE (93/7), 0.00254 [.000100] MIN THK.

3	2-322447-1
5	322447-1
2	322447
FINISH	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: MM[INCHES]		CHK DA PATTERSON 3-17-93				
		APVD JL MECKLEY 3-17-93	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC			
		0 PLC ± -	APPLICATION SPEC			
		1 PLC ± -	—			
		2 PLC ± -	—			
		3 PLC ± -	—			
		4 PLC ± -	—			
		ANGLES ± -	—			
MATERIAL		FINISH	WEIGHT			
- 4		SEE TABLE	—			
			CUSTOMER DRAWING			
			SCALE	8:1	SHEET	1 OF 1
			REV	G		