


Features

- High Voltage to 3000V with Low Leakage
- 1.5kV to 3kV V_{RRM}
- Plastic Package - UL Recognition Flammability Classification 94V-0

NOT RECOMMENDED FOR NEW DESIGN



Mechanical Data

- Case: DO-41 Molded Plastic
- Terminals: Plated Leads Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Approx. Weight: 0.35 grams
- Mounting Position: Any
- Marking: Type Number

DO-41 Plastic		
Dim	Min	Max
A	25.40	—
B	4.06	5.21
C	0.71	0.884
D	2.00	2.72

All Dimensions in mm

Maximum Ratings and Electrical Characteristics

@ $T_A = 25^\circ\text{C}$ unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	R1500F	R2000F	R3000F	Unit
Peak Repetitive Reverse Voltage	V_{RRM}	1500	2000	3000	V
Working Peak Reverse Voltage	V_{VRWM}				
DC Blocking Voltage	V_R				
RMS Reverse Voltage	$V_R(\text{RMS})$	1050	1400	2100	V
Average Rectified Output Current (Note 1)	I_o	500		200	A
@ $T_L = 55^\circ\text{C}$					
Non-Repetitive Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	30		25	A
Forward Voltage @ $I_F = 500\text{mA}$ @ $I_F = 200\text{mA}$	V_{FM}	2.0	3.0	— 6.0	V
Peak Reverse Current at Rated DC Blocking Voltage	I_{RM}		5.0		μA
Typical Junction Capacitance (Note 2)	C_j	9.0		6.0	pF
Typical Reverse Recovery Time (Note 3)	t_{rr}	500			ns
Operating and Storage Temperature Range	T_j, T_{STG}	-65 to +125			°C

Notes:

1. Valid provided that leads are kept at ambient temperature at a distance of 9.5mm from the case.
2. Measured at 1.0 MHz and applied reverse voltage of 4.0V DC.
3. Measured with $I_F = 0.5\text{A}$, $I_R = -1\text{A}$, $I_{rr} = -0.25\text{A}$




Fig. 1 Current Derating for Various Lead Lengths




Fig. 2 Typical Forward Characteristics




Fig. 3 Peak Fwd Surge Current vs # of Cycles @ 60 Hz




Fig. 4 Typical Junction Capacitance