




NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON LABEL
4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010
OF PLUNGER TRAVEL
5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
6 - GOLD BIFURCATED CONTACTS
7 - Ø.047 HOLE FOR WIRE LOCKING

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION

CHARACTERISTICS

```

OPERATING FORCE ----- 2-4 LB
FULL OVERTRAVEL FORCE ----- 15 LB MAX
RELEASE FORCE ----- 1 LB MIN
PRETRAVEL ----- .040 MAX
DIFFERENTIAL TRAVEL ----- .020 MAX
OVERTRAVEL ----- .250 MIN

```

ELECTRICAL DATA

6	CONTACT ARRANGEMENT
	2X S P D T

LOAD	28 VDC	
	SEA LEVEL	50,000 FT
RES	I	I
IND	0.5	0.5

SCALE	FULL
-------	------

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$

ANGLES

WEIGHT 2.0 OZS MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602EN611-RB](#)