

LOC		DIST		REVISIONS					
				DESCRIPTION		DATE	DWN	APVD	
		P	LTR						
			A2	REVISED PER ECR-14-013892		08OCT2014	NK	GJ	

D

C

B



A

D

C

B






A




RECOMMENDED PANEL OPENING DIMENSIONS
FOR CAP HOUSING 1*5 AND 1*4 POSITIONS
(TOLERANCE: ±0.15mm)

- ⚠ MATERIAL:
LEVEL 1:PBT,STANDARD TEMPERATURE 105°C
KEY A:NATURAL; KEY B:PURPLE; KEY C:BLUE; KEY D:YELLOW

LEVEL 2:NYLON,HIGH TEMPERATURE 150°C
KEY A:LIGHT GREY; KEY B:LIGHT GREY; KEY C:LIGHT GREY; KEY D:LIGHT GREY
- ⚠ MATERIAL MARK:
LEVEL 1:PBT,LEVEL 2:HDT
- 3 APPLICABLE CONTACT P/N
TAB CONTACT:1971238/1971780/82/84/86/88-*
- 4 MATING CONN. P/N
PLUG HSG: *-1971773-
TPA (LOCK PLATE): *-1971777-*
- 5 RECOMMENDED PANEL THICKNESS:1.0~2.0mm



RECOMMENDED PANEL OPENING DIMENSIONS
FOR CAP HOUSING 1*3 POSITION
(TOLERANCE: ±0.15mm)











RECOMMENDED PANEL OPENING DIMENSIONS
FOR CAP HOUSING 1*2 POSITION
(TOLERANCE: ±0.15mm)

6 This product has not completed validation testing.

POS	A	B	C	D	E	F	G
1*5	33.70	27.50	39.5	31.30	36.70	31.80	2.9
1*4	27.70	21.50	33.5	25.30	30.70	25.80	2.9
1*3	21.70	15.50	27.5	19.30			2.5
1*2	15.70	9.50	21.5	13.30			1.1

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	06JUL2012		 TE Connectivity		
				CHK	06JUL2012				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	06JUL2012		NAME		
mm				YUZHONG MAO					
		0 P/LC	±	PRODUCT SPEC		CAP HOUSING, PANEL MOUNT, SINGLE ROW POWER TRIPLE LOCK -			
		1 P/LC	±0.35	108-106118					
		2 P/LC	±0.25	APPLICATION SPEC					
		3 P/LC	±	114-106118					
		4 P/LC	±						
ANGLES		±	+			SIZE			
FINISH		-	-						
MATERIAL				WEIGHT		-		CAGE CODE	
									
				Customer Drawing		SCALE		SHEET	
						-			
								1	
								2	
								REV	
								A2	

LOC		DIST		REVISIONS					
-		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-







1*2 POSITIONS

1*3 POSITIONS

1*4 POSITIONS

1*5 POSITIONS



KEYING FOR 1*2 POS.

KEYING FOR 1*3 POS.

KEYING FOR 1*4 POS.

KEYING FOR 1*5 POS.

1*3	LEVEL 1	KEY A	1-1971772-3
		KEY B	2-1971772-3
		KEY C	3-1971772-3
		KEY D	4-1971772-3
	LEVEL 2	KEY A	5-1971772-3
		KEY B	6-1971772-3
		KEY C	7-1971772-3
		KEY D	8-1971772-3
1*2	LEVEL 1	KEY A	1-1971772-2
		KEY B	2-1971772-2
		KEY C	3-1971772-2
		KEY D	4-1971772-2
	LEVEL 2	KEY A	5-1971772-2
		KEY B	6-1971772-2
		KEY C	7-1971772-2
		KEY D	8-1971772-2
POS.	MATERIAL	KEY	P/N

1*4	LEVEL 1	KEY A	1-1971772-4
		KEY B	2-1971772-4
		KEY C	3-1971772-4
		KEY D	4-1971772-4
	LEVEL 2	KEY A	5-1971772-4
		KEY B	6-1971772-4
		KEY C	7-1971772-4
		KEY D	8-1971772-4
1*5	LEVEL 1	KEY A	1-1971772-7
		KEY B	2-1971772-7
		KEY C	3-1971772-7
		KEY D	4-1971772-7
	LEVEL 2	KEY A	5-1971772-7
		KEY B	6-1971772-7
		KEY C	7-1971772-7
		KEY D	8-1971772-7
POS.	MATERIAL	KEY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: TOMMY_WU 06JUL2012
CHK: HAPYE_WU 06JUL2012
APVD: YUZHONG_MAO 06JUL2012

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±.35
1 PLC ±0.25
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±.
FINISH

MATERIAL

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

NAME

TE Connectivity

CAP HOUSING,PANEL MOUNT,SINGLE ROW
POWER TRIPLE LOCK

108-106118

114-106118

Customer Drawing

SCALE

SHEET 2 OF 2

REV A2